Product datasheet

Specification





circuit breaker ComPact NSX250F. 36 kA at 415 VAC. TMD trip unit 250 A. 3 poles 3d

LV431630

! Discontinued on: 15 Jun 2023

! Discontinued

Price: 9,085.79 ZAR

Main

····a···		
Range	ComPact	
Product Name	ComPact NSX	
Range Of Product	ComPact NSX100250	
Device Short Name	NSX250F	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	
Number Of Poles	3P	
Protected Poles Description	3t	
[In] Rated Current	250 A at 40 °C	
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz	
Network Type	AC	
Network Frequency	50/60 Hz	
Suitability For Isolation	Yes conforming to EN/IEC 60947-2	
Utilisation Category	Category A	
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	22 kA at 240 V AC 50/60 Hz conforming to UL 508 22 kA Icu at 525 V AC 50/60 Hz conforming to IEC 60947-2 35 kA Icu at 440 V AC 50/60 Hz conforming to IEC 60947-2 36 kA Icu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 8 kA Icu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 85 kA Icu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 35 kA at 480 V AC 50/60 Hz conforming to UL 508 30 kA Icu at 500 V AC 50/60 Hz conforming to IEC 60947-2 15 kA at 600 V AC 50/60 Hz conforming to UL 508	
Performance Level	F 36 kA 415 V AC	
Trip Unit Name	TM-D	
Trip Unit Technology	Thermal-magnetic	
Trip Unit Protection Functions	Ш	
Control Type	Toggle	
Circuit Breaker Mounting Mode	Fixed	

Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

[Ics] Rated Service Short-Circuit Breaking Capacity	35 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2 36 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 85 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 22 kA at 525 V AC 50/60 Hz conforming to IEC 60947-2 30 kA at 500 V AC 50/60 Hz conforming to IEC 60947-2 8 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2	
Mechanical Durability	20000 cycles	
Electrical Durability	5000 cycles at 690 V In 10000 cycles at 690 V In/2 10000 cycles at 440 V In 20000 cycles at 440 V In/2	
Mounting Support	Backplate	
Upside Connection	Front	
Downside Connection	Front	
Connection Pitch	35 mm	
Protection Type	L : for overload protection (thermal) I : for short-circuit protection (magnetic)	
Trip Unit Rating	250 A at 40 °C	
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable	
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.71 x ln	
Long-Time Protection Delay Adjustment Type Tr	Fixed	
[Tr] Long-Time Protection Delay Adjustment Range	120400 s at 1.5 x ln 15 s at 6 x lr	
Short-Time Protection Pick-Up Adjustment Type Isd	Adjustable	
[Isd] Short-Time Protection Pick- Up Adjustment Range	510 x ln	
Short-Time Protection Delay Adjustment Type Tsd	Fixed	
Earth-Leakage Protection	Without	
Number Of Slots For Electrical Auxiliaries	5 slot(s)	
Width (W)	105 mm	
Height (H)	161 mm	
Depth (D)	86 mm	
Net Weight	2.4 kg	

Environment

Standards	EN/IEC 60947	
Product Certifications	CCC Marine EAC	
Overvoltage Category	Class II	
Electrical Shock Protection Class	Class II	
Pollution Degree	3 conforming to IEC 60664-1	
Ip Degree Of Protection	IP40 conforming to IEC 60529	
Ik Degree Of Protection	IK07 conforming to IEC 62262	
Ambient Air Temperature For Operation	-2570 °C	
Ambient Air Temperature For Storage	-5085 °C	

Relative Humidity	095 %
Operating Altitude	02000 m without derating 2000 m5000 m with derating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.9 cm
Package 1 Width	11.4 cm
Package 1 Length	19.5 cm
Package 1 Weight	2.006 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	12
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	24.694 kg

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information