Product datasheet

Specification





EasyLogic

EasyLogic PM2100

EasyLogic PM2110. Power & Energy meter. Total Harmonic. LED display. Pulse. class 1

METSEPM2110

Price: 5,412.24 ZAR

Main Range

Product Name

Device Short Name	PM2110
Product Or Component Type	Power meter
Complementary	
Device Application	Power monitoring Sub billing
Power Quality Analysis	total harmonic distortion
Type Of Measurement	Total current harmonic distortion THD (I) per phase Total voltage harmonic distortion THD (U) per phase Apparent energy total Active and reactive energy total Apparent power total Active and reactive power total Current average Voltage average Frequency average Power factor average
Metering Type	Peak demand power PM, QM, SM Apparent power S, S1, S2, S3 Current I, I1, I2, I3

	Active, reactive, apparent energy (signed, four quadrant)
Accuracy Class	Class 1 active energy conforming to IEC 62053-21 Class 1 reactive energy conforming to IEC 62053-24
Measurement Accuracy	Apparent power +/- 1 %
	Active energy +/- 1 %
	Reactive energy +/- 1 %
	Active power +/- 1 %
	Voltage +/- 0.5 %
	Power factor +/- 0.01
	Current +/- 0.5 %
	Frequency +/- 0.05 %
Measurement Current	56000 mA

35...480 V AC 50/60 Hz between phases 20...277 V AC 50/60 Hz between phase and neutral 480...999000 V AC 50/60 Hz with external VT

Reactive power Q, Q1, Q2, Q3 Calculated neutral current

Peak demand currents Unbalance current Demand power P, Q, S Active power P, P1, P2, P3

Voltage U, U21, U32, U13, V, V1, V2, V3

Frequency Measurement Range 45...65 Hz

Measurement Voltage

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"



[Us] Rated Supply Voltage	44277 V AC 4565 Hz +/- 10 % 44277 V DC +/- 10 %
Network Frequency	60 Hz 50 Hz
Ride-Through Time	100 ms 120 V AC typical 400 ms 230 V AC typical 50 ms 125 V DC typical
[In] Rated Current	5 A 1 A
Maximum Power Consumption In Va	6 VA at 277 V AC
Maximum Power Consumption In W	3.3 W (power lines (AC)) 2 W at 277 V (power lines (DC))
Input Impedance	Current (impedance <= 0.3 mOhm) Voltage (impedance > 5 MOhm)
Tamperproof Of Settings	Protected by access code
Display Type	7 segments LED
Display Colour	Red
Messages Display Capacity	3 fields of 4 characters
Display Digits	12 digit(s) - 14.2 mm in height
Demand Intervals	Configurable from 1 to 60 min
Information Displayed	Demand current (past value) Demand current (present value) Demand power (past value) Demand power (present value) Voltage Current Frequency Energy consumption Harmonic distortion Power factor Active power Apparent power Reactive power Unbalanced in %
Control Type	3 x button
Local Signalling	Red LED: output signal 19999000 pulse/ k_h (kWh, kVAh, kVARh) Green LED: module operating (RUN)
Number Of Inputs	0
Number Of Outputs	1 pulse
Pop Parameter	Pulse: 20 ms (540 V DC, 20 mA max)19999000 pulse/ k_h (kWh, kVAh, kVARh)
Impulse Duration	20 ms
Communication Port Protocol	POP
Sampling Rate	64 samples/cycle
Cybersecurity	Enable/disable communication ports
Communication Service	Remote monitoring
Product Certifications	CE conforming to IEC 61010-1 CULus conforming to UL 61010-1 CULus conforming to CSA C22.2 No 61010-1 RCM EAC C-Tick
Mounting Mode	Clip-on
Mounting Position	Vertical

Mounting Support	Framework
Provided Equipment	1 x installation guide
Measurement Category	Category II 480 V Category II 480600 V
Electrical Insulation Class	Double insulation Class II
Flame Retardance	V-0 conforming to UL 94
Connections - Terminals	Current transformer: screw connection (bottom) 6 Voltage inputs: screw connection (top) 4
Material	Polycarbonate
Width	96 mm
Depth	76.09 mm total: 61.64 mm embedded:
Height	96 mm
Net Weight	300 g
Compatibility Code	PM2110

Environment

Service Life	7 year(s)
Ip Degree Of Protection	IP54 front: conforming to IEC 60529 IP30 body: conforming to IEC 60529
Relative Humidity	595 % at 50 °C
Pollution Degree	2
Ambient Air Temperature For Operation	-1060 °C
Ambient Air Temperature For Storage	-2570 °C
Operating Altitude	<= 2000 m
Electromagnetic Compatibility	Electrostatic discharge conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test conforming to IEC 61000-4-4 Surge immunity test conforming to IEC 61000-4-5 Conducted RF disturbances conforming to IEC 61000-4-6 Magnetic field at power frequency conforming to IEC 61000-4-8 Voltage dips and interruptions immunity test conforming to IEC 61000-4-11 Emission tests conforming to FCC part 15 class A
Overvoltage Category	III

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.94 cm
Package 1 Width	12.19 cm
Package 1 Length	9.14 cm
Package 1 Weight	0.41 kg

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

19 Apr 2024