# **Product datasheet**

Specification





PC box IP66 IK08 RAL7035 Int.H325W275D120 Ext.H341W291D128 opaque PC cover H20

NSYTBP342912

Price: 1,160.32 ZAR

#### Main

Range	Thalassa	
Product Name	Thalassa TBP	
Device Application	Multi-purpose	
Category	Industrial box	
Height	341 mm	
Width	291 mm	
Depth	128 mm	
Internal Height	325 mm	
Internal Width	275 mm	
Internal Depth	120 mm	
Enclosure Mounting	Wall mounted	
Device Composition	1 body	
	1 cover	
	4 cover screw	
Body Type	One piece moulded	
Type Of Front Cover	Low plain cover	
Cover Fixing	Plastic screws	
Lock Type	Captive screw flat outside sealed area	
Removable Parts	Cover by captive screws	

## Complementary

Material	Polycarbonate	
Colour	Grey (RAL 7035)	
Standards	IEC 62208 UL 508 A	
Product Certifications	TÜV UL	
Electrical Insulation Class	Class II	
Mounting Location	Outdoor (with canopy or shelter and anticondensation valve)	
Net Weight	1.16 kg	

#### **Environment**

Ip Degree Of Protection IP66 conforming to NEMA 4.4X

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Ik Degree Of Protection	IK08 conforming to IEC 62262
Fire Resistance	960 °C
Ambient Air Temperature For Storage	-1560 °C
Operating Temperature	-2580 °C

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.0 cm
Package 1 Width	30.0 cm
Package 1 Length	35.5 cm
Package 1 Weight	1.57 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	4
Package 2 Height	40.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	7.058 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	48
Package 3 Height	136.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	102.5 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>9</b>	Toxic Heavy Metal Free	
<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information