

Product datasheet

Specifications



Conext TL-8KVA Inverter

PVSNVC8000

⚠ Discontinued on: 07 Jan 2021

⚠ End-of-service on: 28 Feb 2021

⚠ Discontinued

Price: 95,866.31 ZAR

Main

Range Of Product	Conext TL
Device Short Name	TL 8000 E
Product Or Component Type	Grid-tie solar inverter
Network Number Of Phases	3 phases
Nominal Output Power	8 kVA

Complementary

Photovoltaic Power	8.3 kW input power for maximal output power
Output Voltage	230/400 V AC (nominal)
Number Of Mppt	2
Maximum Output Current	12.8 A AC
Frequency	50/60 Hz +/- 3 Hz output
Cos Phi	0.8 (leading to lagging)
Harmonic Distortion	< 3 % at rated power
Input Voltage	<= 1000 V DC open circuit 350...850 V DC MPPT 200 V DC at start
Input Current Per Mppt	17 A
Efficiency	97.4 % European 98.2 % peak
Maximum Power Consumption In W	2 W - night time
Topology	Transformerless
Function Available	Dry contact Remote inverter disable Standard integrated DC disconnect Embedded data logger for 365 days
Communication Interface	Modbus (RS485)
Connector Type	- (IP67) for output Multicontact MC4 for input
Type Of Cooling	Fan
Height	62.5 cm
Width	61.2 cm
Depth	27.8 cm

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	41 kg
Enclosure Material	Aluminium
Marking	CE

Environment

Ip Degree Of Protection	IP55 (balance) IP65 (electronic)
Ambient Air Temperature For Operation	-20...60 °C
Electromagnetic Compatibility	Emission standard for residential, commercial and light-industrial environments conforming to EN 61000-6-3 Immunity for industrial environments conforming to EN 61000-6-2
Standards	CEI 0-21 RD 1699 UTE C 15-712-1 VDE-AR-N 4105 IEC 61727 IEC 62116 AS 4777 EN 50438 VDE 0126
Operating Altitude	< 2000 m without derating
Relative Humidity	4...100 % condensing
Directives	2006/95/EC - low voltage directive 2004/108/EC - electromagnetic compatibility