Product datasheet

Specifications





Harmony. Modular timing relay. 0.7 A. 1 s..100 h. off delay. solid state output. 24...240 V AC

RE17LCBM

Price: 1,522.08 ZAR

Main

Mani		
Range Of Product	Harmony Timer Relays	
Product Or Component Type	Single function relay	
Discrete Output Type	Solid state	
Width	17.5 mm	
Component Name	RE17L	
Time Delay Type	Off-delay	
Time Delay Range	10100 h 660 s 660 min 110 h 110 s 110 min 0.11 s	
Nominal Output Current	0.7 Δ	

Complementary

Control Type	Selector switch front panel	
[Us] Rated Supply Voltage	24240 V AC 50/60 Hz	
Voltage Range	0.851.1 Us	
Supply Frequency	5060 Hz +/- 5 %	
Release Of Input Voltage	7 V	
Control Signal Pulse Width	0.05 s typical	
Insulation Resistance	100 MOhm at 500 V DC conforming to IEC 60664-1	
[Uimp] Rated Impulse Withstand Voltage	5 kV during 1.2/50 μs	
Power On Delay	100 ms	
Connections - Terminals	Screw terminals, $1 \times 0.51 \times 3.3 \text{ mm}^2$ (AWG 20AWG 12) solid without cable end Screw terminals, $2 \times 0.52 \times 2.5 \text{ mm}^2$ (AWG 20AWG 14) solid without cable end Screw terminals, $1 \times 0.21 \times 2.5 \text{ mm}^2$ (AWG 24AWG 14) flexible with cable end Screw terminals, $2 \times 0.22 \times 1.5 \text{ mm}^2$ (AWG 24AWG 16) flexible with cable end	
Tightening Torque	0.61 N.m conforming to IEC 60947-1	
Dielectric Strength	2.5 kV 1 mA/1 minute 50 Hz conforming to IEC 61812-1	
Housing Material	Self-extinguishing	
Repeat Accuracy	+/- 0.5 % conforming to IEC 61812-1	
Temperature Drift	+/- 0.05 %/°C	
Voltage Drift	+/- 0.2 %/V	

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Setting Accuracy Of Time Delay	+/- 10 % of full scale at 25 °C conforming to IEC 61812-1	
Reset Time	350 ms on de-energisation typical	
On-Load Factor	100 %	
Power Consumption In Va	03 VA at 240 V AC	
Breaking Capacity	0.5 A AC conforming to UL 0.7 A AC at 20 °C	
Operating Frequency	10 Hz	
Maximum Output Current	20 A	
Minimum Switching Current	10 mA	
Maximum Leakage Current	5 mA	
Maximum Switching Voltage	250 V AC	
Maximum Voltage Drop	<4 V 3-wire <8 V 2-wire	
Electrical Durability	100000000 cycles	
Marking	CE	
Creepage Distance	4 kV/3 conforming to IEC 60664-1	
Safety Reliability Data	MTTFd = 353.8 years B10d = 320000	
Mounting Position	Any position in relation to normal vertical mounting plane	
Mounting Support	35 mm DIN rail conforming to IEC 60715	
Net Weight	0.068 kg	
Time Delay Type	С	
Functionality	Off-delay timing	
Number Of Functions	1	
Compatibility Code	RE17	

Environment

Immunity To Microbreaks	20 ms
Derating Factor	5 mA/°C
Standards	2004/108/EC IEC 61000-6-3 2006/95/EC IEC 61000-6-2 IEC 61000-6-4 IEC 61000-6-4
Product Certifications	CSA GL cULus
Ambient Air Temperature For Storage	-3060 °C
Ambient Air Temperature For Operation	-2060 °C
Ip Degree Of Protection	IP20 (terminal block) conforming to IEC 60529 IP40 (housing) conforming to IEC 60529 IP50 (front panel) conforming to IEC 60529
Vibration Resistance	20 m/s² (f= 10150 Hz) conforming to IEC 60068-2-6
Shock Resistance	15 gn for 11 ms conforming to IEC 60068-2-27
Relative Humidity	93 % without condensation conforming to IEC 60068-2-30

Electromagnetic Compatibility

Electrostatic discharge immunity test: (in contact), level 3, 6 kV, conforming to IEC 61000-4-2

Electrostatic discharge immunity test: (in air), level 3, 8 kV, conforming to IEC 61000-4-2

Susceptibility to electromagnetic fields: (80 MHz to 1 GHz), level 3, 10 V/m, conforming to IEC 61000-4-3

Electrical fast transient/burst immunity test: (capacitive connecting clip), level 3, 1 kV, conforming to IEC 61000-4-4

Electrical fast transient/burst immunity test: (direct), level 3, 2 kV, conforming to IEC 61000-4-4

1.2/50 μs shock waves immunity test: (differential mode), level 3, 1 kV, conforming to IEC 61000-4-5

1.2/50 μs shock waves immunity test: (common mode), level 3, 2 kV, conforming to IEC 61000-4-5

Conducted RF disturbances: (0.15...80 MHz), level 3, 10 V, conforming to IEC 61000-4-6 $\,$

Voltage dips and interruptions immunity test: (1 cycle), 0 %, conforming to IEC 61000-4-11

Voltage dips and interruptions immunity test: (25/30 cycles), 70 %, conforming to IEC 61000-4-11

Conducted and radiated emissions: , class B, conforming to EN 55022

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	7.8 cm
Package 1 Length	9.5 cm
Package 1 Weight	71.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	40
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.348 kg

Sustainability Green Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information


Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Dimensions Drawings


Width 17.5 mm




RE17LCBM

Connections and Schema

Internal Wiring Diagram



Wiring Diagram



RE17LCBM


Technical Description

Function C: Off-Delay Relay with Control Signal


Description

After power-up and closing of the control contact C, the output R closes. When control contact C re-opens, timing T starts. At the end of the timing period, the output(s) R revert(s) to its/their initial state. The second output can be either timed or instantaneous

Function: 1 Output



Function: 2 Outputs



2 timed outputs (R1/R2) or 1 timed output (R1) and 1 instantaneous output (R2 inst.)

RE17LCBM

Legend

