Product datasheet

Specifications





Harmony. Modular 3-phase supply control relay. 5 A. 2 CO. 208...440 V AC

RM17TG20

Price: 1,987.27 ZAR

Main

mann	
Range Of Product	Harmony Control Relays
Relay Type	Control relay
Product Or Component Type	3-phase control relay
Product Specific Application	For 3-phase supply
Relay Name	RM17TG
Relay Monitored Parameters	Phase sequence Phase failure detection (2 or more phase cut)
Time Delay	Without
Switching Capacity In Va	1250 VA
Measurement Range	208480 V AC
Contacts Type And Composition	2 C/O
[Uc] Control Circuit Voltage	208440 V

Complementary

Maximum Switching Voltage	250 V AC 250 V DC	
Minimum Switching Current	10 mA at 5 V DC	
[Un] Rated Nominal Voltage	, self-powered	
Supply Voltage Limits	183484 V AC	
Control Circuit Voltage Limits	- 12 % + 10 % Un	
Power Consumption In Va	022 VA at 400 V AC 50 Hz	
Voltage Detection Threshold	< 100 V AC	
Control Circuit Frequency	5060 Hz +/- 10 %	
Output Contacts	2 C/O	
Nominal Output Current	5 A	
Measurement Voltage Limits	183484 V AC	
Delay At Power Up	650 ms	
Voltage Range	183484 V	
Response Time	<= 130 ms (in the event of a fault)	
Marking	CE	
Overvoltage Category	III conforming to IEC 60664-1	
Insulation Resistance	> 500 MOhm at 500 V DC conforming to IEC 60255-5 > 500 MOhm at 500 V DC conforming to IEC 60664-1	

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

400 V conforming to IEC 60664-1
50/60 Hz +/- 10 %
Any position without derating
Screw terminals, 1 x 0.51 x 4 mm² (AWG 20AWG 11) solid without cable end Screw terminals, 2 x 0.52 x 2.5 mm² (AWG 20AWG 14) solid without cable end Screw terminals, 1 x 0.21 x 2.5 mm² (AWG 24AWG 12) flexible with cable end Screw terminals, 2 x 0.22 x 1.5 mm² (AWG 24AWG 16) flexible with cable end
0.61 N.m conforming to IEC 60947-1
Self-extinguishing plastic
LED (yellow) for relay ON
35 mm symmetrical DIN rail conforming to IEC 60715
10000 cycles
30000000 cycles
<= 360 operations/hour full load
AC-12 conforming to IEC 60947-5-1 AC-13 conforming to IEC 60947-5-1 AC-14 conforming to IEC 60947-5-1 AC-15 conforming to IEC 60947-5-1 DC-12 conforming to IEC 60947-5-1 DC-13 conforming to IEC 60947-5-1
B10d = 850000 MTTFd = 924.6 years
17.5 mm
0.13 kg
Without test button

Environment

Electromagnetic Compatibility	Emission standard for industrial environments conforming to IEC 61000-6-4 Emission standard for residential, commercial and light-industrial environments
	conforming to IEC 61000-6-3
	Immunity for industrial environments conforming to IEC 61000-6-2
Standards	IEC 60255-1
Product Certifications	GOST
	C-Tick
	UL
	CSA
	GL
Directives	73/23/EEC - low voltage directive
	89/336/EEC - electromagnetic compatibility
Ambient Air Temperature For Storage	-4070 °C
Ambient Air Temperature For Operation	-2050 °C
Relative Humidity	95 % at 55 °C conforming to IEC 60068-2-30
Vibration Resistance	0.35 mm (f= 557.6 Hz) conforming to IEC 60068-2-6
	1 gn (f= 57.6150 Hz) conforming to IEC 60255-21-1
Shock Resistance	15 gn for 11 ms conforming to IEC 60255-21-1
Ip Degree Of Protection	IP20 (terminals) conforming to IEC 60529
	IP30 (casing) conforming to IEC 60529
Pollution Degree	3 conforming to IEC 60664-1
Dielectric Test Voltage	2 kV, 1 min AC 50 Hz
Non-Dissipating Shock Wave	4 kV

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.700 cm
Package 1 Width	7.800 cm
Package 1 Length	9.700 cm
Package 1 Weight	98.000 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	48
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.150 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	768
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	87.204 kg

Contractual warranty

10 May 2024

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

3.54

Dimensions Drawings

3-Phase Supply Control Relays

Dimensions and Mounting




RM17TG20

Connections and Schema


3-Phase Supply Control Relays

Wiring Diagram



Application Scheme

Example




(1) Fault

Technical Description

Function Diagram

Phase Sequence Control and Total Loss of Phase Detection



Legend

Tr Response time on appearance of a fault

L1, L2, L3 Phases of the supply voltage monitored

R - R1/R2 Output relay(s),

Relay status: black color = energized.