





APC Smart-UPS SRT, 10000VA, 230V

SRT10KXLI

Price: 107,015.57 ZAR

Overview

Presentation	High density, double-conversion on-line power protection with scalable runtime.	
Lead Time	Usually in Stock	
Main		
Main Input Voltage	230 V	
	400 V 3 phases	
Other Input Voltage	220 V	
	240 V	
	380 V	
	415 V	
Main Output Voltage	230 V	
Other Output Voltage	220 V	
	240 V	
Rated Power In W	10000 W	
Rated Power In Va	10000 VA	
Output Connection Type	6 IEC 60320 C13	
	3 IEC Jumpers	
	4 IEC 60320 C19	
Output Connector Type	Hard wire 3-wire (H N + E) 1	
Provided Equipment	CD with software	
	Documentation CD	
	Installation guide	
	Temperature probe	
	USB cable	
	Warranty card	

Batteries & Runtime

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Battery Type	Lead-acid battery
Number Of Battery Filled Slots	0
Battery Recharge Time	1.5 h
Number Of Battery Replacement Quantity	2
Battery Voltage	+/- 192 V (split battery referenced to neutral)
Battery Charger Power	876 W rated
Battery Life	35 year(s)

Web/SNMP management card

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Replacement Battery	APCRBC140 ☐
Extended Runtime	1

General

Ups Type	Double conversion online
Product Web Sub-Family	High density
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

•	
Colour	Black
Height	43.2 cm
Width	26.3 cm
Depth	71.5 cm
Net Weight	111.82 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Rack-mounted with kit
Two Post Mountable	0
Usb Compatible	Yes

Input

Network Frequency	4070 Hz auto-sensing
Number Of Input Connectors	1 hard wire 3-wire (1P + N + E) 1 hard wire 5-wire (3P + N + E)
Input Voltage Limits	100275 V adjustable (half load) 173 476 V adjustable (half load)

Output

Maximum Configurable Power In Va	10000 VA
Maximum Configurable Power In W	10000 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Wave Type	Sine wave
Harmonic Distortion	Less than 2 %
Crest Factor	3:1
Bypass Type	Internal bypass (automatic and manual)

Conformance

Product Certifications	CE	
	EAC	
	IRAM	
	RCM	
	VDE	

Marking	CE Mark
Standards	EN/IEC 62040-1:2019/A11:2021
	EN/IEC 62040-2:2006/AC:2006
	EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For Operation	040 °C
Relative Humidity	095 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-1545 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	0.0015240.00 m
Acoustic Level	55 dBA
Heat Dissipation	1947 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	1
Preinstalled Device	Network management card 3 with environmental monitoring
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off	Yes

Surge Protection and Filtering

Surge Energy Rate 480 J

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	46.1 cm
Package 1 Width	60 cm
Package 1 Length	100 cm
Package 1 Weight	126.554 kg

Contractual warranty

Warranty 3 years repair or replace (excluding battery) and 2 years for battery

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >









Energy Efficient Take-back Transparency RoHS/REACh

Resource performance



Energy Efficient Product



Take-Back Program Available

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information