

Product datasheet

Specifications



Small panel with keypad, matrix screen, green, 122 x 32 pixels, 24V DC

XBTR410

⚠ Discontinued on: 15 Dec 2021

⚠ To be end-of-service on: 30 Jun 2029

⚠ Discontinued - Service only

Main

Range Of Product	Magelis XBTR
Display Resolution	122 x 32 pixels
Software Type	Configuration software
Software Designation	Vijeo Designer Lite
Operating System	Windows

Complementary

Display Type	Matrix backlit LCD
Character Font	Latin Katakana Greek Cyrillic Chinese (simplified Chinese)
Supply Voltage Limits	18...30 V
Residual Ripple	<= 1200 MV
Power Consumption In W	5 W
Number Of Key	20
Number Of Fixed Keys	8
Number Of Customisable Keys	12
Number Of Pages	256 alarm pages 200 application pages
Memory Type	Flash
Memory Capacity	512 KB
Integrated Connection Type	Serial link: female SUB-D 25, asynchronous transmission mode (RS232C/RS485) multidrop topology Power supply: removable screw terminal block
Realtime Clock	Access to the PLC real-time clock
Range Compatibility	Twido Modicon TSX Micro Modicon Quantum Modicon Momentum Modicon Premium Modicon M340
Product Mounting	Flush mounting
Fixing Mode	By 4 spring clips

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Display Material	Polyester
Front Material	PPT
Keypad Material	Polyester
Marking	CE
Height	118 mm
Width	137 mm
Depth	39 mm
Cut-Out Dimensions	119.6 (+/- 0.5) x 105.2 (+/- 0.4) mm
Net Weight	0.55 kg

Environment

Product Or Component Type	Small panel with keypad
Display Colour	Green
Display Capacity	1 line of 5 characters minimum 4 lines of 20 characters maximum
[Us] Rated Supply Voltage	24 V DC
Supply	External source
Downloadable Protocols	Third party protocols Modbus Uni-TE
Standards	UL 508 IEC 60068-2-27 IEC 60068-2-6 IEC 61131-2 CSA C22.2 No 14
Product Certifications	CSA Class 1 Division 2 ATEX zone 2/22 UL Class 1 Division 2 UL 1604
Ambient Air Temperature For Operation	0...55 °C
Ambient Air Temperature For Storage	-20...60 °C
Relative Humidity	0...85 % without condensation
Ip Degree Of Protection	IP20 (rear panel) conforming to IEC 60529 IP65 (front panel) conforming to IEC 60529
Nema Degree Of Protection	NEMA 4X front panel (outdoor use)
Shock Resistance	15 gn for 11 ms
Vibration Resistance	+/- 3.5 mm (f= 2...8.45 Hz) 1 gn (f= 8.45...150 Hz)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.8 cm
Package 1 Width	17.5 cm
Package 1 Length	25.0 cm
Package 1 Weight	603.0 g
Unit Type Of Package 2	S03

Number Of Units In Package 2	10
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	6.686 kg

Contractual warranty

Warranty	18 months
-----------------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Reach Regulation [REACH Declaration](#)


Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)

Weee The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Dimensions




a		a1 (1)		b		b1 (1)		P3 (2)		P4 (3)	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
137	5.39	160	6.29	118	5	146	6	58	2.28	104	4.09

- (1) With fixing clips (included with product)
- (2) P3: depth with 25-way SUB-D angled cable XBTZ9680 (for Twido, TSX Micro and Premium) or XBTZ998 (for Modicon STB)
- (3) P4: depth with 25-way SUB-D cable XBTZ68/Z9681(for Twido, TSX Micro and Premium)

Mounting and Clearance

Cut-out for Flush Mounting



Panel thickness = 1.5...6 mm / 0.05...0.23 in.

H		G		r max.	
±0.4 mm	±0.02 in.	±0.5 mm	±0.02 in.	mm	in.
105.2	4.14	119.6	5	1.5	0.05