
Product datasheet

Specifications






MOUNTING PLATE NSX/CVS/ VIGI 250 V. FIX.ROT.HANDLE

03041

() Discontinued on: 15 Jun 2023



Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Mounting plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure
Installation Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Installed Device	EasyPact: fixed CVS100160 without earth leakage protection - control: direct front rotary handle - vertical installation EasyPact: fixed CVS250 without earth leakage protection - control: direct front rotary handle - vertical installation ComPact: fixed NSX100160 without earth leakage protection - control: direct front rotary handle - vertical installation ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation ComPact: fixed NSX250 without earth leakage protection - control: direct front rotary handle - vertical installation EasyPact: fixed CVS100160 with earth leakage protection - control: direct front rotary handle - vertical installation EasyPact: fixed CVS250 with earth leakage protection - control: direct front rotary handle - vertical installation ComPact: fixed NSX100160 with earth leakage protection - control: direct front rotary handle - vertical installation ComPact: fixed NSX100160 with earth leakage protection - control: direct front rotary handle - vertical installation ComPact: fixed NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation ComPact: fixed NSX250 with earth leakage protection - control: direct front rotary handle - vertical installation
Poles Description	4 x 3P: fixed CVS100160 vertical installation 3 x 4P: fixed CVS100160 vertical installation 4 x 3P: fixed CVS250 vertical installation 3 x 4P: fixed CVS250 vertical installation 4 x 3P: fixed NSX100160 vertical installation 3 x 4P: fixed NSX100160 vertical installation 4 x 3P: fixed NSX250 vertical installation 3 x 4P: fixed NSX250 vertical installation
Condition Of Lloing Coble Tic	Need additional aloge (ANA birb) where is shall then affide the is in write al

Condition Of Using Cable Tie Need ad

Need additional plate (1M high) when installation of device is in vertical

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of
10 module(s): NSX100160 with earth leakage protection , direct with long terminal
enclosure)
in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of
13 module(s): CVS250 with earth leakage protection, direct with long terminal shield
in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of enclosure)
13 module(s): CVS250 with earth leakage protection , direct with long terminal shield
shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of
10 module(s): CVS100160 with earth leakage protection , direct with long terminal
enclosure)
shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of
10 module(s): CVS100160 with earth leakage protection , direct with long terminal
enclosure)
shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of
11 module(s): NSX250 without earth leakage protection , direct with long terminal
enclosure)
shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of
11 module(s): NSX250 without earth leakage protection, direct with long terminal
bottom of enclosure)
terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or
9 module(s): NSX100160 without earth leakage protection , direct with long
bottom of enclosure)
terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or
9 module(s): NSX100160 without earth leakage protection , direct with long
shield in 600 mm Widewall-mounted enclosure (cable coming from top or bottom of enclosure)
11 module(s): CVS250 without earth leakage protection, direct with long terminal shield in 600 mm Widewall mounted applesure (solid coming from top or bottom of
enclosure)
shield in 600 mm Widefloor-standing enclosure (cable coming from top or bottom of
11 module(s): CVS250 without earth leakage protection , direct with long terminal
bottom of enclosure)
terminal shield in 600 mm Widewall-mounted enclosure (cable coming from top or
9 module(s): CVS100160 without earth leakage protection , direct with long
bottom of enclosure)
terminal shield in 600 mm Widefloor-standing enclosure (cable coming from top or

Complementary

Cable Entry	Cut-out plates 0.36 mm top or bottom 167 mm Cut-out plates 0.31 mm top or bottom 267 mm
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Matt Smooth
Colour	White (RAL 9001)
Width	600 mm
Height	150 mm
Net Weight	0.84 kg

Functional Unit

600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 9 0.36 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 9 0.36 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 9 0.36 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 9 0.36 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 11 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 11 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS250 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 11 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 11 0.31 mm 600 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 9 0.36 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 9 0.36 mm 600 mm Prisma G floor-standing enclosure ComPact NSX100...160 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 9 0.36 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 9 0.36 mm 600 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 11 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 without fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 11 0.31 mm 600 mm Prisma G floor-standing enclosure ComPact NSX250 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 11 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 without fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 11 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 with fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 10 0.36 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 with fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 10 0.36 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS100...160 with fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 10 0.36 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS100...160 with fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 10 0.36 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS250 with fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 13 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 with fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 13 0.31 mm 600 mm Prisma G floor-standing enclosure EasyPact CVS250 with fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 13 0.31 mm 600 mm Prisma G wall-mounted enclosure EasyPact CVS250 with fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 13 0.31 mm 600 mm Prisma G floor-standing enclosure ComPact NSX100...160 with fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 10 0.36 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 with fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 10 0.36 mm 600 mm Prisma G floor-standing enclosure ComPact NSX100...160 with fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 10 0.36 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX100...160 with fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 10 0.36 mm 600 mm Prisma G floor-standing enclosure ComPact NSX250 with fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 13 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 with fixed direct front rotary handle vertical 3P 4 direct with long terminal shield 13 0.31 mm 600 mm Prisma G floor-standing enclosure ComPact NSX250 with fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 13 0.31 mm 600 mm Prisma G wall-mounted enclosure ComPact NSX250 with fixed direct front rotary handle vertical 4P 3 direct with long terminal shield 13 0.31 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.800 cm
Package 1 Width	15.200 cm
Package 1 Length	47.000 cm
Package 1 Weight	840.000 g

Unit Type Of Package 2	S04
Number Of Units In Package 2	14
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	12.560 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	56
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	50.240 kg

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Halogen Free Plastic Parts Product

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile