



### Main

Range	Prisma
Range compatibility	Prisma P
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Type of front plate	Cut-out
Installed device	Masterpact : fixed NW08...16 - control: toggle - vertical installation Masterpact : fixed NW20...25 - control: toggle - vertical installation Masterpact : fixed NW32 - control: toggle - vertical installation
Poles description	1 x 3P : mounting plate support : NW08...16 vertical installation 1 x 4P : mounting plate support : NW08...16 vertical installation 1 x 3P : mounting plate support : NW20...25 vertical installation 1 x 4P : mounting plate support : NW20...25 vertical installation 1 x 3P : mounting plate support : NW32 vertical installation 1 x 4P : mounting plate support : NW32 vertical installation
Operating position	Horizontal

### Complementary

Enclosure/Cubicle description	Cubicle - width 650 mm, depth 600 mm Cubicle - width 650 mm, depth 1000 mm
Connection position	Front connection Rear connection
Number of vertical modules [50 mm]	9
Standards	IEC 61439-2 IEC 61439-1
Product certifications	ASEFA
Quantity per set	Set of 1
Height	450 mm
Width	500 mm
Product weight	1.54 kg
Material	Steel
Surface finish	Matt Smooth

Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White RAL 9001

## Environment

IK degree of protection	IK07 conforming to EN/IEC 62262
-------------------------	---------------------------------

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0807 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Available

## Contractual warranty

Warranty period	18 months
-----------------	-----------