

# Product datasheet

Specifications



## power supply module Modicon Quantum - 115 V/230 V AC - summable or standalone

140CPS11420

Discontinued on: 31 Dec 2022

To be end-of-service on: 31 Dec 2030

To be discontinued

Price: 29,324.51 ZAR

### Main

Range Of Product	Modicon Quantum automation platform
Product Or Component Type	Power supply module
Power Supply Type	Summable or standalone

### Complementary

Input Voltage	115 V (93...132 V) AC 47...63 Hz 230 V (170...276 V) AC
Input Current	1300 mA at 115 V 750 mA at 230 V
Inrush Current	19 A 230 V 38 A 115 V
Rated Power In Va	130 VA
Associated Fuse Rating	2 A, slow-blow
Harmonic Distortion	<= 10 % of fundamental rms value
Output Voltage	5.1 V DC
Power Supply Output Current	11 A 60 °C standalone 20 A 60 °C summable
Output Overvoltage Protection	Internal
Output Overload Protection	Internal
Power Dissipation	6 + (1.5 x Iout) where Iout is in A
Alarm Output	1 NC 6 A 220 V power supply fault
Local Signalling	1 LED (green) for power (PWR OK)
Marking	CE
Module Format	Standard
Net Weight	0.65 kg

### Environment

Standards	UL 508 CSA C22.2 No 142
Product Certifications	cUL
Resistance To Electrostatic Discharge	4 kV contact conforming to IEC 801-2 8 kV on air conforming to IEC 801-2

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Resistance To Electromagnetic Fields	10 V/m 80...2000 MHz conforming to IEC 801-3
Ambient Air Temperature For Operation	0...60 °C
Ambient Air Temperature For Storage	-40...85 °C
Relative Humidity	95 % without condensation
Operating Altitude	<= 5000 m

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.49 cm
Package 1 Width	16.3 cm
Package 1 Length	31.08 cm
Package 1 Weight	785.4 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	7
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	6133.5 g
Unit Type Of Package 3	P12
Number Of Units In Package 3	168
Package 3 Height	95 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	156204 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability



**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Mercury Free	
	Rohs Exemption Information	<a href="#">Yes</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>	
China Rohs Regulation	<a href="#">China RoHS declaration</a>	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	<a href="#">End of Life Information</a>	

Dimensions Drawings

Racks for Modules Mounting

Dimensions of Modules and Racks




- (1) 2 slots
- (2) 3 slots
- (3) 4 slots
- (4) 6 slots
- (5) 10 slots
- (6) 16 slots

Connections and Schema

115/230 Vac, 11 A Summable Power Supply Module

Wiring Diagram



NOTE: A normally closed relay contact rated at 220 Vac, 6 A / 30 Vdc, 5 A is available on terminals 1 and 2 of the power terminal strip. This contact set may be used to signal input power OFF.