# **Product datasheet**

Specifications





circuit breaker ComPact NS1600N. 50 kA at 415 VAC. Micrologic 2.0 A trip unit. 1600 A. fixed.3 poles 3d

33263

① To be discontinued

() Discontinued on: 31 Mar 2024

### Price: 88,253.01 ZAR

#### Main

mann	
Range	ComPact
Product Name	ComPact NS
Range Of Product	ComPact NS630b1600
Device Short Name	Compact NS1600N
Product Or Component Type	Circuit breaker
Device Application	Distribution
Number Of Poles	3P
Protected Poles Description	3D
(In) Rated Current Up To 65 °C	1600 A at 50 °C
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
Network Type	AC
Network Frequency	50/60 Hz
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Utilisation Category	Category B
[Icu] Rated Ultimate Short-Circuit Breaking Capacity	30 kA lcu at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 50 kA lcu at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 50 kA lcu at 440 V AC 50/60 Hz conforming to IEC 60947-2 85 kA lcu at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 40 kA lcu at 500/525 V AC 50/60 Hz conforming to IEC 60947-2
Performance Level	N 50 kA 415 V AC
Trip Unit Name	MicroLogic 2.0 A
Trip Unit Technology	Electronic
Trip Unit Protection Functions	LI
Control Type	Rotary handle Toggle
Circuit Breaker Mounting Mode	Fixed

### Complementary

[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

[Ics] Rated Service Short-Circuit Breaking Capacity	30 kA at 500/525 V AC 50/60 Hz conforming to IEC 60947-2 37 kA at 220/240 V AC 50/60 Hz conforming to IEC 60947-2 37 kA at 380/415 V AC 50/60 Hz conforming to IEC 60947-2 22 kA at 660/690 V AC 50/60 Hz conforming to IEC 60947-2 37 kA at 440 V AC 50/60 Hz conforming to IEC 60947-2
[Icw] Rated Short-Time Withstand Current	19.2 kA 1 s conforming to IEC 60947-2
Mechanical Durability	10000 cycles
Electrical Durability	1000 cycles at 690 V In 2000 cycles at 690 V In/2 2000 cycles at 440 V In 5000 cycles at 440 V In/2
Power Losses	74 W
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front
Connection Pitch	70 mm
Protection Type	L : for overload protection (long time) I : for instantaneous short-circuit protection
Trip Unit Rating	1600 A at 50 °C
Long-Time Pick-Up Adjustment Type Ir (Thermal Protection)	Adjustable 9 settings
[Ir] Long-Time Protection Pick-Up Adjustment Range	0.41 x ln
Long-Time Protection Delay Adjustment Type Tr	Adjustable 9 settings
[Tr] Long-Time Protection Delay Adjustment Range	12.5600 s at 1.5 x lr 0.524 s at 6 x lr 0.716.6 s at 7.2 x lr
Thermal Memory	20 mn
Instantaneous Protection Pick-Up Adjustment Type li	Adjustable
[li] Instantaneous Protection Pick- Up Adjustment Range	1.510 x lr
Earth-Leakage Protection	Without
Zone Selective Interlocking Zsi	Without
Auxiliary Contact Composition	1 NO/NC
Local Signalling	4 LEDs (red) for fault indication 1 LED (yellow) for overload
Display Type	LCD display
Type Of Measurement	Ammeter
Width (W)	210 mm
Height (H)	327 mm
Depth (D)	147 mm
Net Weight	14 kg

### Environment

Standards	EN/IEC 60947-2
Product Certifications	ASEFA ASTA
Pollution Degree	3 conforming to IEC 60947
Ip Degree Of Protection	IP40 conforming to IEC 60529

Ik Degree Of Protection	IK07 conforming to EN 50102
Ambient Air Temperature For Operation	-2570 °C
Ambient Air Temperature For Storage	-4085 °C
Relative Humidity	095 %
Operating Altitude	02000 m without derating 2000 m5000 m with derating

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23.0 cm
Package 1 Width	37.0 cm
Package 1 Length	39.5 cm
Package 1 Weight	13.223 kg

### **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Mercury Free

Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information