# **Product datasheet**

Specifications





# residual current protection relay. VigiPacT RH99M. 30 mA to 30 A. 380/415 VAC 50/60 Hz. DIN rail mounting

56174

### Price: 10,263.56 ZAR

#### Main

Range	VigiPacT
Device Short Name	RH99M
Product Or Component Type	Residual current protection relay
Relay Application	Protection relay
Mounting Support	DIN rail
Earth-Leakage Protection Class	Туре А
Type Of Setting	Selector
Residual Earth-Leakage Sensitity Adjustment Type	Adjustable 9 settings
Earth-Leakage Sensitivity	0.0330 A
Earth-Leakage Time Delay	Instantaneous for 0.03 A Adjustable 9 settings 04.5 s for 0.0330 A
Current Sensors Compatibility	VigiPacT TOA earth leakage current sensor VigiPacT A earth leakage current sensor VigiPacT L earth leakage current sensor
[Ithe] Conventional Enclosed Thermal Current	8 A
Minimum Load	10 mA at 12 V
[Us] Rated Supply Voltage	380415 V AC 50/60 Hz 55110 %
Power Consumption In Va	4 VA
Monitored Distribution System	1000 V - AC at 50/60 Hz (maximum) 1000 V - AC at 400 Hz (maximum)
Earthing System	TT IT TN-S
[Uimp] Rated Impulse Withstand Voltage	8 kV
Reset	Manual reset

### Complementary

Test Function	Local Remote test
Monitoring	Electronics (continuous) Power supply (continuous) Relay/sensor link (continuous)
Type Of Measurement	Earth fault current internal measurement, range: 80100 %
Tamperproof Of Settings	Protected by sealable cover

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

• ·· · · ·	
Connections - Terminals	Auxiliary power supply: terminal block cable(s) 0.22.5 mm <sup>2</sup> flexible AWG 24AWG 12
	Auxiliary power supply: terminal block cable(s) 0.22.5 mm <sup>2</sup> rigid AWG 24AWG 12 Auxiliary power supply: terminal block cable(s) 0.252.5 mm <sup>2</sup> flexible AWG
	24AWG 12
	Fault: screw terminal cable(s) 0.22.5 mm <sup>2</sup> flexible AWG 24AWG 12
	Fault: screw terminal cable(s) 0.24 mm <sup>2</sup> rigid AWG 24AWG 12
	Fault: screw terminal cable(s) 0.252.5 mm <sup>2</sup> flexible AWG 24AWG 12
	Relay test and fault reset: screw terminal cable(s) 0.141 mm <sup>2</sup> flexible AWG 26AWG 16
	Relay test and fault reset: screw terminal cable(s) 0.141.5 mm <sup>2</sup> rigid AWG
	26AWG 16 Relay test and fault reset: screw terminal cable(s) 0.250.5 mm <sup>2</sup> flexible AWG
	26AWG 16
	Sensor: screw terminal cable(s) 0.141 mm <sup>2</sup> flexible AWG 26AWG 16 Sensor: screw terminal cable(s) 0.141.5 mm <sup>2</sup> rigid AWG 26AWG 16
	Sensor: screw terminal cable(s) 0.250.5 mm² flexible AWG 26AWG 16
	Voltage presence: screw terminal cable(s) 0.22.5 mm <sup>2</sup> flexible AWG 24AWG 12
	Voltage presence: screw terminal cable(s) 0.24 mm <sup>2</sup> rigid AWG 24AWG 12
	Voltage presence: screw terminal cable(s) 0.252.5 mm² flexible AWG 24AWG 12
Wire Stripping Length	Auxiliary power supply: 7 mm for top connection
	Fault: 8 mm for bottom connection
	Relay test and fault reset: 5 mm for bottom connection
	Sensor: 5 mm for top connection
	Voltage presence: 8 mm for bottom connection
Fightening Torque	Auxiliary power supply: 0.6 N.m top
	Fault: 0.6 N.m bottom
	Relay test and fault reset: 0.25 N.m bottom
	Sensor: 0.25 N.m top
	Voltage presence: 0.6 N.m bottom
9 Mm Pitches	6
Standards	EN/IEC 60947-2 Annex M
	EN/IEC 60755
	UL 1053
	CAN/CSA C22.2 No. 144
Width	54 mm
Height	81 mm
Depth	74 mm
Net Weight	0.3 kg
p Degree Of Protection	IP40 on front face: conforming to EN/IEC 60529
	IP30 on side parts: conforming to EN/IEC 60529
	IP20 on connection terminals: conforming to EN/IEC 60529
Ik Degree Of Protection	IK07 conforming to EN 50102
Ik Degree Of Protection Mechanical Robustness	IK07 conforming to EN 50102 Fire resistance conforming to IEC 60695-2-1
-	-
-	Fire resistance conforming to IEC 60695-2-1

### Environment

Overvoltage Category	IV
Electrical Shock Protection Class	Class II
Electromagnetic Compatibility	Conducted and radiated emissions: , B, conforming to CISPR 11 Conducted radio-frequency immunity test: , 3, conforming to IEC 61000-4-6 Electrostatic discharge immunity test: , 4, conforming to IEC 61000-4-2 High-energy conducted susceptibility: , 4, conforming to IEC 61000-4-5 Low-energy conducted susceptibility: , 4, conforming to IEC 61000-4-4 Radiated susceptibility: , 3, conforming to IEC 61000-4-3
Relative Humidity	95 % at 55 °C
Pollution Degree	3 conforming to IEC 60664-1
Ambient Air Temperature For Operation	-3570 °C

Ambient Air	Temperature For	-5585 °C
Storage		

# **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.500 cm
Package 1 Width	9.000 cm
Package 1 Length	7.600 cm
Package 1 Weight	275.000 g
Unit Type Of Package 2	\$03
Number Of Units In Package 2	36
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	10.388 kg

# Contractual warranty

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information