# **Product datasheet**

Specifications



# Rack PDU, Metered, 1U, 12A/ 208V, 10A/230V, (8) C13

AP7820B

Overview		
Lead Time	Usually in Stock	
Main		
Pdu Type	Metered	
Cord Length	1.98 m	
Provided Equipment	Cord retention bracket(s) Installation guide Rack mounting brackets User manual	

#### Complementary

· · · · · · · · · · · · · · · · · ·	
Input Voltage	200 V
	208 V
	230 V
	200 1
Height	4.4 cm
Width	44.4 cm
Output Voltage	208 V
	230 V
Depth	10.2 cm
	( 70 )
Net Weight	1.73 kg
Mounting Location	Front
	Rear
Mounting Preference	No preference
Input Plug Type	IEC 60320 C14
Mounting Mode	Rack-mounted
Rack Units	1U
Mounting Position	Horizontal
[In] Rated Current	10 A
Input Current Limits	15 A
Load Capacity	2300 VA
Rated Current	10 A - 230 V
	12 A - 208 V
Network Frequency	50/60 Hz
Total Number Of Outlets	8 IEC 60320 C13

#### Environment

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Product Certifications	cUL listed C-Tick CE CSA GOST UL listed VDE VCCI
Standards	FCC part 15 class A UL 60950
Ambient Air Temperature For Operation	-545 °C
Relative Humidity	595 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2565 °C
Storage Relative Humidity	595 %
Storage Altitude	0.0015240.00 m

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.4 cm
Package 1 Width	33.7 cm
Package 1 Length	47 cm
Package 1 Weight	2.91 kg

# **Contractual warranty**

Warranty

2 years repair or replace

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



#### **Resource performance**

Energy Efficient Product

✓ Take-Back Program Available

#### Well-being performance

0	Lead Free	
	Mercury Free	
	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information