





APC NetShelter SX, Server Rack Enclosure, 48U, without Sides and Doors, Black, 2258H x 600W x 1070D mm

AR3107X617

Overview

Lead Time Usually in Stock

Main

Product Or Component Type	Rack enclosure
Number Of Rack Unit	48U
Provided Equipment	Baying hardware Key(s) Leveling feet Mounting hardware Pre-installed casters

Physical

Height	225.8 cm
Width	60 cm
Depth	107 cm
Net Weight	84.09 kg
Colour	Black
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	91.49 cm
Minimum Mounting Depth	19.1 cm
Rack Width	19"
Marking	14 gauge EIA mounting rail 0 gauge front door 16 gauge post 0 gauge rear door 18 gauge roof 0 gauge side panels
Permanent Permissible Load	1020.58 kg dynamic 1360.78 kg static

Conformance

 Standards
 UL 2416

 UL 60950-1
 EIA-310E

Packing Units

Unit Type Of Package 1 PCE

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Number Of Units In Package 1	1
Package 1 Height	238.5 cm
Package 1 Width	121.9 cm
Package 1 Length	89.9 cm
Package 1 Weight	103.55 kg

Contractual warranty

Warranty 5 year repair or replace



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance

✓ Reach Free Of Svhc
 ✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile