# **Product datasheet**

Specification





TeSys K contactor - 3P - AC-3 <= 440 V 9 A - 1 NC aux. - 380...400 V AC coil

LC1K0901Q7

Price: 583.85 ZAR

### Main

Range	TeSys
Product Or Component Type	Contactor
Device Application	Control
Contactor Application	Motor control Resistive load
Complementary	
Utilisation Category	AC-3
	AC-3e
	AC-1
	AC-4
Poles Description	3P
Power Pole Contact Composition	3 NO
[Ue] Rated Operational Voltage	Power circuit: <= 690 V AC <= 400 Hz
to the second second	Signalling circuit: <= 690 V AC <= 400 Hz
	Organism gonodic - 000 v //O - 400 Hz
[le] Rated Operational Current	9 A (at <60 °C) at <= 440 V AC AC-3 for power circuit
	9 A (at <60 °C) at <= 440 V AC AC-3e for power circuit
	20 A (at <60 °C) at <= 690 V AC AC-1 for power circuit
	25.7 (at 50 b) at 1 000 t 710 ft of for power oriotic
Control Circuit Type	AC at 50/60 Hz
[Uc] Control Circuit Voltage	380400 V AC 50/60 Hz
Motor Power Kw	2.2 kW at 220230 V AC 50/60 Hz AC-3
	4 kW at 380415 V AC 50/60 Hz AC-3
	4 kW at 440/690 V AC 50/60 Hz AC-3
	2.2 kW at 220230 V AC 50/60 Hz AC-3e
	4 kW at 380415 V AC 50/60 Hz AC-3e
	4 kW at 440/690 V AC 50/60 Hz AC-3e
	2.2 kW at 220230 V AC 50/60 Hz AC-4
	4 kW at 380415 V AC 50/60 Hz AC-4
	4 kW at 440/690 V AC 50/60 Hz AC-4
Auxiliary Contact Composition	1 NC
[Uimp] Rated Impulse Withstand Voltage	8 kV
Overvoltage Category	III
[Ith] Conventional Free Air	20 A (at 60 °C) for power circuit
Thermal Current	10 A (at 50 °C) for signalling circuit
	(
Irms Rated Making Capacity	110 A AC for power circuit conforming to IEC 60947
	110 A AC for signalling circuit conforming to IEC 60947
Rated Breaking Capacity	110 A at 220230 V conforming to IEC 60947
	110 A at 380400 V conforming to IEC 60947
	110 A at 415 V conforming to IEC 60947
	110 A at 440 V conforming to IEC 60947
	80 A at 500 V conforming to IEC 60947
	70 A at 600 , 600 V and farming to 150 60047

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

70 A at 660...690 V conforming to IEC 60947

[Icw] Rated Short-Time Withstand	90 A 50 °C - 1 s for power circuit
Current	85 A 50 °C - 5 s for power circuit
	80 A 50 °C - 10 s for power circuit
	60 A 50 °C - 30 s for power circuit 45 A 50 °C - 1 min for power circuit
	40 A 50 °C - 3 min for power circuit
	20 A 50 °C - >= 15 min for power circuit
	80 A - 1 s for signalling circuit
	90 A - 500 ms for signalling circuit
	110 A - 100 ms for signalling circuit
Associated Fuse Rating	25 A gG at <= 440 V for power circuit
-	25 A aM for power circuit
	10 A gG for signalling circuit conforming to IEC 60947
	10 A gG for signalling circuit conforming to VDE 0660
Average Impedance	3 mOhm - Ith 20 A 50 Hz for power circuit
Insulation Resistance	> 10 MOhm for signalling circuit
Inrush Power In Va	30 VA (at 20 °C)
Hold-In Power Consumption In Va	4.5 VA (at 20 °C)
Heat Dissipation	1.3 W
Control Circuit Voltage Limits	Operational: 0.81.15 Uc (at <50 °C)
	Drop-out: >= 0.20 Uc (at <50 °C)
Connections - Terminals	Screw clamp terminals 1 cable(s) 1.54 mm²solid
Commodation Terminals	Screw clamp terminals 1 cable(s) 1.54 mm solid  Screw clamp terminals 1 cable(s) 0.754 mm²flexible without cable end
	Screw clamp terminals 1 cable(s) 0.342.5 mm²flexible with cable end
	Screw clamp terminals 2 cable(s) 1.54 mm²solid
	Screw clamp terminals 2 cable(s) 0.754 mm²flexible without cable end
	Screw clamp terminals 2 cable(s) 0.341.5 mm²flexible with cable end
Maximum Operating Rate	3600 cyc/h
Auxiliary Contacts Type	type instantaneous 1 NC
Signalling Circuit Frequency	<= 400 Hz
Minimum Switching Current	5 mA for signalling circuit
Minimum Switching Voltage	17 V for signalling circuit
Operating Time	1020 ms coil de-energisation and NO opening
	1020 ms coil energisation and NO closing
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
cares, riemanine, zerei	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO
	13849-1
Non Overlap Distance	0.5 mm
Mechanical Durability	10 Mcycles
Electrical Durability	1.3 Mcycles 9 A AC-3 at Ue <= 440 V
	1.3 Mcycles 9 A AC-3 at Ue <= 440 V
	0.16 Mcycles 20 A AC-1 at Ue <= 690 V
	0.02 Mcycles 54 A AC-4 at Ue <= 440 V
Mechanical Robustness	Shocks contactor closed, on X axis: 10 Gn for 11 ms conforming to IEC 60068-2-27
	Shocks contactor closed, on Y axis: 15 Gn for 11 ms conforming to IEC 60068-2-27
	Shocks contactor closed, on Z axis: 15 Gn for 11 ms conforming to IEC 60068-2-27
	Shocks contactor opened, on X axis: 6 Gn for 11 ms conforming to IEC 60068-2-27
	Shocks contactor opened, on Y axis: 10 Gn for 11 ms conforming to IEC 60068-2-27
	Shocks contactor opened, on Z axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations contactor closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6
	Vibrations contactor closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations contactor opened: 2 Gn, 5300 Hz conforming to IEC 60068-2-6
Height	58 mm
Width	45 mm
Depth	57 mm

### **Environment**

Standards	EN/IEC 60947-4-1 GB/T 14048.4 UL 60947-4-1 CSA C22.2 No 60947-4-1 JIS C8201-4-1
Product Certifications	CB Scheme CCC UL CSA EAC CE
Protective Treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Operating Altitude	2000 m without derating
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	4.800 cm	
Package 1 Width	6.000 cm	
Package 1 Length	6.500 cm	
Package 1 Weight	177.000 g	
Unit Type Of Package 2	S02	
Number Of Units In Package 2	50	
Package 2 Height	nt 15.000 cm	
Package 2 Width	30.000 cm	
Package 2 Length	40.000 cm	
Package 2 Weight	9.305 kg	

# **Contractual warranty**

Warranty 18 months

### Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
End of Life Information