## **Product datasheet**

Specification





# TeSys K reversing contactor - 3P - AC-3 <= 440 V 6 A - 1 NO - 48 V AC coil

LC2K0610E7

Price: 1,658.05 ZAR

## Main

Range	TeSys	
Product Name	TeSys K	
Product Or Component Type	Reversing contactor	
Device Short Name	LC2K	
Device Application	Control	
Contactor Application	Motor control	
Utilisation Category	AC-3 AC-3e AC-4	
Device Presentation	Preassembled with reversing power busbar	
Poles Description	3P	
Power Pole Contact Composition	3 NO	
[Ue] Rated Operational Voltage	Power circuit: 690 V AC 50/60 Hz Signalling circuit: <= 690 V AC 50/60 Hz	
[le] Rated Operational Current	6 A (at <60 °C) at <= 440 V AC AC-3 for power circuit 6 A (at <60 °C) at <= 440 V AC AC-3e for power circuit	
Motor Power Kw	1.5 kW at 220230 V AC 50/60 Hz 2.2 kW at 380415 V AC 50/60 Hz 3 kW at 440/690 V AC 50/60 Hz	
Control Circuit Type	AC at 50/60 Hz	
[Uc] Control Circuit Voltage	48 V AC 50/60 Hz	
Auxiliary Contact Composition	1 NO	
[Uimp] Rated Impulse Withstand Voltage	8 kV	
Overvoltage Category	III	
[lth] Conventional Free Air Thermal Current	20 A (at 60 °C) for power circuit 10 A (at 50 °C) for signalling circuit	
Irms Rated Making Capacity	I Making Capacity  110 A AC for power circuit conforming to IEC 60947  110 A AC for signalling circuit conforming to IEC 60947	
Rated Breaking Capacity	110 A at 220230 V conforming to IEC 60947 110 A at 380400 V conforming to IEC 60947 110 A at 415 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 70 A at 660690 V conforming to IEC 60947	

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"



[Icw] Rated Short-Time Withstand	00 A 50 °C . 1 a for naugo aircuit
Current	90 A 50 °C - 1 s for power circuit 85 A 50 °C - 5 s for power circuit
	80 A 50 °C - 10 s for power circuit
	60 A 50 °C - 30 s for power circuit
	45 A 50 °C - 1 min for power circuit
	40 A 50 °C - 3 min for power circuit
	20 A 50 °C - >= 15 min for power circuit
	80 A - 1 s for signalling circuit
	90 A - 500 ms for signalling circuit 110 A - 100 ms for signalling circuit
	- Took Too Ho tor Signaling Ground
Associated Fuse Rating	25 A gG at <= 440 V for power circuit
	25 A aM for power circuit
	10 A gG for signalling circuit conforming to IEC 60947
	10 A gG for signalling circuit conforming to VDE 0660
Average Impedance	3 mOhm - Ith 20 A 50 Hz for power circuit
[Ui] Rated Insulation Voltage	Power circuit: 600 V conforming to UL 508
	Power circuit: 690 V conforming to IEC 60947-4-1
	Signalling circuit: 690 V conforming to IEC 60947-4-1
	Signalling circuit: 690 V conforming to IEC 60947-5-1
	Signalling circuit: 600 V conforming to UL 508
	Power circuit: 600 V conforming to CSA C22.2 No 14
	Signalling circuit: 600 V conforming to CSA C22.2 No 14
Electrical Durability	1.3 Mcycles 6 A AC-3 at Ue <= 440 V
	1.3 Mcycles 6 A AC-3e at Ue <= 440 V
	0.05 Mcycles 36 A AC-4 at Ue <= 440 V
Interlocking Type	Mechanical
Mounting Support	Rail
g -upp-	Plate
Standards	EN/IEC 60947-4-1
	GB/T 14048.4
	UL 60947-4-1
	CSA C22.2 No 60947-4-1 JIS C8201-4-1
	010 00201-4-1
Product Certifications	CB Scheme
	CCC
	UL
	CSA
	EAC CE
	UKCA
One and the second second	
Connections - Terminals	Screw clamp terminals 1 cable(s) 1.54 mm²solid
	Screw clamp terminals 1 cable(s) 0.754 mm²flexible without cable end Screw clamp terminals 1 cable(s) 0.342.5 mm²flexible with cable end
	Screw clamp terminals 1 cable(s) 0.542.3 mm nexible with cable end  Screw clamp terminals 2 cable(s) 1.54 mm²solid
	Screw clamp terminals 2 cable(s) 0.754 mm²flexible without cable end
	Screw clamp terminals 2 cable(s) 0.341.5 mm²flexible with cable end
Tightoning Tormina	0.0 4.0 Nov. or a server description of the DMT. No. 0
Tightening Torque	0.81.3 N.m on screw clamp terminals Philips No 2
	0.81.3 N.m - on screw clamp terminals flat Ø 6 mm 0.81.3 N.m - on screw clamp terminals pozidriv No 2
	· · · · · · · · · · · · · · · · · · ·
Operating Time	1020 ms coil energisation and NO closing
	1020 ms coil de-energisation and NO opening
Safety Reliability Level	B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO
	13849-1
Mechanical Durability	5 Mcycles
	,
Maximum Operating Rate	3600 cyc/h
•	
Complementary	
Control Circuit Voltage Limits	Operational: 0.81.15 Uc (at <50 °C)
<b>9</b>	Drop-out: 0.20.75 Uc (at <50 °C)
Inrush Power In Va	30 VA (at 20 °C)

Hold-In Power Consumption In Va	4.5 VA (at 20 °C)	
Heat Dissipation	1.3 W	
Auxiliary Contacts Type	type instantaneous 1 NO	
Signalling Circuit Frequency	<= 400 Hz	
Minimum Switching Current	5 mA for signalling circuit	
Minimum Switching Voltage	17 V for signalling circuit	
Non Overlap Distance	0.5 mm	
Insulation Resistance	> 10 MOhm for signalling circuit	

## **Environment**

Ip Degree Of Protection	IP20 conforming to VDE 0106	
Protective Treatment	TC conforming to IEC 60068 TC conforming to DIN 50016	
Ambient Air Temperature For Operation	-2550 °C	
Ambient Air Temperature For Storage	-5080 °C	
Operating Altitude	2000 m without derating	
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102	
Mechanical Robustness	Shocks contactor closed, on X axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Y axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor closed, on Z axis: 15 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on X axis: 6 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Y axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks contactor opened, on Z axis: 10 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations contactor closed: 4 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations contactor opened: 2 Gn, 5300 Hz conforming to IEC 60068-2-6	
Height	58 mm	
Width	90 mm	
Depth	57 mm	
Net Weight	0.39 kg	

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	6.5 cm
Package 1 Length	9.2 cm
Package 1 Weight	363.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	25
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.575 kg

## **Contractual warranty**

Warranty

18 months

19 Apr 2024



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes


#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information


**Dimensions Drawings** 

#### **Dimensions**

Reversing Contactors LC2 K, LP2 K, LP5 K: Mounting on Panel




Reversing Contactors LC2 K, LP2 K, LP5 K: Mounting on Rail AM1 DP200 or AM1 DE200 (35 mm)



Connections and Schema

Wiring

3-Pole Reversing Contactors with Screw Clamp Connections: 3P + N/O



3-Pole Reversing Contactors with Screw Clamp Connections: 3P + N/C

