# **Product datasheet**

Specifications





# TeSys LRF - electronic thermal overload relay - 200...330 A - class 20

LR9F7575

() Discontinued on: 31 Dec 2023

#### ① To be discontinued

#### Price: 16,749.68 ZAR

#### Main

Range	TeSys
Product Name	TeSys LRF
Device Short Name	LR9F
Product Or Component Type	Electronic thermal overload relay
Relay Application	Motor protection
Product Compatibility	LC1F225LC1F500
Network Type	AC
Thermal Overload Class	Class 20 conforming to IEC 60947-4
Thermal Protection Adjustment Range	200330 A

## Complementary

Network Frequency	50/60 Hz
Mounting Support	Direct on contactor Plate
Tripping Threshold	1.12 +/- 0.06 In tripping conforming to IEC 60947-4-1
Surge Withstand	4 kV conforming to IEC 61000-4-5
Contacts Type And Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	5 A for control circuit
[Ue] Rated Operational Voltage	1000 V AC 50/60 Hz for power circuit conforming to VDE 0110 group C
[Ui] Rated Insulation Voltage	Power circuit: 1000 V AC conforming to IEC 60947-4
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-1
Phase Failure Sensitivity	Tripping in 4 s +/- 20 % conforming to IEC 60947-4-1
Reset	Manual reset on front relay
Control Type	Dial white full-load current adjustment Test button red Push-button red reset Push-button stop
Local Signalling	Trip indicator
Temperature Compensation	-2070 °C
Current Consumption	<= 5 mA no-load
Switching Capacity For Alarm	0150 mA

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Maximum Voltage Drop	<2.5 V closed state	
Connections - Terminals	Control circuit: screw clamp terminals 1 cable 0.752.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 1 cable 0.752.5 mm <sup>2</sup> - cable stiffness: solid Control circuit: screw clamp terminals 1 cable 0.754 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable 11.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 2 cable 12.5 mm <sup>2</sup> - cable stiffness: flexible - with cable end Control circuit: screw clamp terminals 2 cable 12.5 mm <sup>2</sup> - cable stiffness: flexible - without cable end Control circuit: screw clamp terminals 2 cable 12.5 mm <sup>2</sup> - cable stiffness: solid Power circuit: lugs-ring terminals M10	
Tightening Torque	Control circuit: 1.2 N.m on screw clamp terminals Power circuit: 35 N.m on screw clamp terminals	
Height	136.8 mm	
Width	150 mm	
Depth	127.6 mm	
Net Weight	2.32 kg	

## Environment

Standards	IEC 60255-8
	VDE 0660
	IEC 60255-17
	EN 60947-4-1
	IEC 60947-4-1
Product Certifications	CSA
	UL
	UKCA
Protective Treatment	тн
Ip Degree Of Protection	IP20 conforming to IEC 60529
	IP20 conforming to VDE 0106
Ambient Air Temperature For Operation	-2055 °C conforming to IEC 60255-8
Ambient Air Temperature For Storage	-4085 °C
Operating Altitude	<= 2000 m without derating
Fire Resistance	850 °C conforming to IEC 60695-2-1
Mechanical Robustness	Shocks: 13 Gn for 11 ms conforming to IEC 60068-2-7
	Vibrations 5300 Hz: 2 GN conforming to IEC 60068-2-6
Dielectric Strength	6 kV 50 Hz conforming to IEC 255-5
Electromagnetic Compatibility	Resistance to electrostatic discharge: 6 kV in indirect mode conforming to IEC 61000-4-2
	Resistance to electrostatic discharge: 8 kV in air conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test: 10 V/m conforming to IEC 61000-4-3
	Fast transients immunity test: 2 kV conforming to IEC 61000-4-4

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	17.2 cm
Package 1 Width	18.0 cm
Package 1 Length	26.0 cm
Package 1 Weight	1.884 kg
Unit Type Of Package 2	S04

Number Of Units In Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	12.144 kg

# **Contractual warranty**

Warranty

18 months

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Mercury Free
Rohs Exemption Information Yes
Pvc Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information