Product datasheet

Specification





(!) Discontinued

LV429629 - Switch-Disconnector Compact NSX100NA - 100 A - 3P.

LV429629

! Discontinued on: 15 Jun 2023

Price: 3,221.93 ZAR

Main

Mani	
Range	ComPact
Product Name	ComPact NSX
Product Or Component Type	Switch disconnector
Device Short Name	Compact NSX100NA
Poles Description	3P
Network Type	AC DC
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz conforming to IEC 60947-3 750 V DC 3 poles in series conforming to IEC 60947-3 500 V DC 2 poles in series conforming to IEC 60947-3 250 V DC 1 pole conforming to IEC 60947-3
[le] Rated Operational Current	AC-22A: 100 A AC 50/60 Hz 220690 V AC-23A: 100 A AC 50/60 Hz 220690 V DC-22A: 100 A DC 250 V 1 pole DC-22A: 100 A DC 500 V 2 poles in series DC-23A: 100 A DC 250 V 1 pole DC-23A: 100 A DC 500 V 2 poles in series
[Ui] Rated Insulation Voltage	800 V AC 50/60 Hz conforming to IEC 60947-3
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-3
[Ith] Conventional Free Air Thermal Current	100 A at 60 °C
[Icm] Rated Short-Circuit Making Capacity	330 kA with upstream protection circuit breaker 2.6 kA switch-disconnector alone
Breaking Capacity Code	NA
Suitability For Isolation	Yes conforming to EN 60947-3 Yes conforming to IEC 60947-3
Contact Position Indicator	Yes
Visible Break	No
Pollution Degree	3 conforming to IEC 60664-1

Complementary

•	,
Control Type	Toggle
Mounting Mode	Fixed
Mounting Support	Backplate
Upside Connection	Front
Downside Connection	Front

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

0.69 kA during 20 s conforming to IEC 60947-3
1.8 kA during 1 s conforming to IEC 60947-3
1.8 kA during 3 s conforming to IEC 60947-3
50000 cycles conforming to IEC 60947-3
AC-22A: 10000 cycles 250 V DC In/2 (1 pole) conforming to IEC 60947-3
AC-22A: 15000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-3
AC-22A: 20000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-3
AC-22A: 35000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-3
AC-22A: 5000 cycles 500 V DC In (2 poles in series) conforming to IEC 60947-3
AC-22A: 8000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-3
AC-23A: 10000 cycles 250 V DC In/2 (1 pole) conforming to IEC 60947-3
AC-23A: 15000 cycles 690 V AC 50/60 Hz In/2 conforming to IEC 60947-3
AC-23A: 20000 cycles 440 V AC 50/60 Hz In conforming to IEC 60947-3
AC-23A: 35000 cycles 440 V AC 50/60 Hz In/2 conforming to IEC 60947-3
AC-23A: 5000 cycles 500 V DC In (2 poles in series) conforming to IEC 60947-3
AC-23A: 8000 cycles 690 V AC 50/60 Hz In conforming to IEC 60947-3
35 mm
161 mm
105 mm
86 mm

Environment

Standards	EN/IEC 60947 UL 508
Product Certifications	EAC CCC
Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Electrical Shock Protection Class	Class II
Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-5585 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.6 cm
Package 1 Width	14.2 cm
Package 1 Length	19.0 cm
Package 1 Weight	1.764 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm
Package 2 Weight	21.934 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information