



# TeSys D - contactor coil - LX4D7 - 24 V DC standard for 80 A contactor

LX4D7BD

! Discontinued on: 13 Mar 2024

! Discontinued

Price: 4,033.97 ZAR

## Main

Range	TeSys
Product Or Component Type	Contactor coil
Device Short Name	LX4D7
Inductance Of Closed Circuit	1.89 H
Product Compatibility	LC1D80
Mechanical Durability	10 Mcycles
Maximum Operating Rate	3600 cyc/h 60 °C

## Complementary

Coil Technology	Without built-in suppressor module
Time Constant	75 ms
Inrush Power In W	22 W (at 20 °C)
Hold-In Power Consumption In W	22 W at 20 °C

### **Environment**

Ambient Air Temperature For Operation	-560 °C
Net Weight	0.68 kg

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.0 cm
Package 1 Width	8.5 cm
Package 1 Length	12.5 cm
Package 1 Weight	638.0 g

## **Contractual warranty**

Morront	40	
Warranty	y 18 months	

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations