



## Main

Range	TeSys
Product or component type	Contactor coil
Device short name	LXD3
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	400 V AC 50/60 Hz
Average resistance	607 Ohm at 20 °C
Inductance of closed circuit	33.1 H
Product compatibility	LC1DT80A LC1D40A...D65A LC1DT60A
Mechanical durability	6 Mcycles
Operating rate	3600 cyc/h at <= 60 °C

## Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.3...0.6 Uc at 60 °C drop-out 50/60 Hz 0.8...1.1 Uc at 60 °C operational 50 Hz 0.85...1.1 Uc at 60 °C operational 60 Hz
Inrush power in VA	160 VA at 20 °C (cos f 0.75) 60 Hz 160 VA at 20 °C (cos f 0.75) 50 Hz
Hold-in power consumption in VA	15 VA at 20 °C (cos f 0.3) 50 Hz 15 VA at 20 °C (cos f 0.3) 60 Hz
Heat dissipation	4...5 W at 50/60 Hz

## Environment

Ambient air temperature for operation	-5...60 °C
Product weight	0.07 kg

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0629 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
Product environmental profile	Available

---

Product end of life instructions	Available
----------------------------------	-----------

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---