

Product datasheet

Specifications



Spacial SF bottom and top frame - 1600x500 mm

NSYSFC166

Price: 11,354.13 ZAR

Main

Range	PanelSeT
Accessory / Separate Part Category	Enclosure accessory
Application	Multi-purpose
Product Or Component Type	Framework kit
For Enclosure Nominal Dimensions	- H: 2000 mm W: 1600 mm D: 600 mm
Mounting Location	Bottom of vertical uprights Top of vertical uprights
Range Compatibility	PanelSeT rear panel PanelSeT side panel PanelSeT vertical upright
Device Composition	1 bottom frame 1 roof 1 top frame
Quantity Per Set	Set of 1

Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Fixing Mode	By screws - each corner of enclosure location
Width	1600 mm
Depth	600 mm external:

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	62.0 cm
Package 1 Length	161.0 cm
Package 1 Weight	39.0 kg
Unit Type Of Package 2	P2M
Number Of Units In Package 2	12
Package 2 Height	80.0 cm
Package 2 Width	200.0 cm

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	120.0 cm
Package 2 Weight	522.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information