Product datasheet

Specifications





Spacial SF transparent door - 2000x800 mm

NSYSFD208T

Price: 9,302.49 ZAR

Main

Range	Spacial
Accessory / Separate Part Category	Enclosure accessory
Product Or Component Type	Door
Application	Multi-purpose
For Enclosure Nominal Dimensions	-
Mounting Location	Front Side
Range Compatibility	Spacial Spacial SF
Device Composition	door lock with handle and 5 mm double bar insert locking bar system 4 points hinges locking bar catches
Quantity Per Set	Set of 1

Complementary

Material	Door: Securit glass Door: sheet steel
Colour	Grey (RAL 7035)
Surface Finish	Epoxy-polyester powder
Lock Type	Lock 5 mm double bar
Number Of Locks	1
Door Type	External transparent
Door Opening Side	Reversible (120 °)
Height	2000 mm nominal:
Width	800 mm nominal:

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	72.5 cm
Package 1 Length	208.5 cm
Package 1 Weight	25.0 kg

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations