# **Product datasheet**

Specification





# SCREW TERMINAL. FEED THROUGH. 2 POINTS. 6MM<sup>2</sup>. BLUE

NSYTRV62BL

**Price: 50.46 ZAR** 

### Main

Range	Linergy	
Product Name	Linergy TR	
Product Or Component Type	Terminal block	
Device Short Name	TRV	
Accessory / Separate Part Category	Connection accessory	
Terminal Block Type	Passthrough	
Terminal Block Level	vel 1	
Mounting Mode	e Clip-on	
Nominal Cross Section	ection 6 mm²	
Length	47.7 mm	
Colour	Blue	
Quantity Per Set	y Per Set Set of 50	

## Complementary

Width	8.2 mm	
Height	47.5 mm	
Connections - Terminals	1 x screw terminal: upstream (M4) 1 x screw terminal: downstream (M4)	
Number Of Connections	2	
Connection Position	Sideways	
Number Of Measurement Input	2	
Cable Cross Section	0.210 mm², solid cable with cable end 0.26 mm², flexible cable with cable end 0.210 mm², solid cable without cable end 0.210 mm², flexible cable without cable end	
Tightening Torque	1.51.8 N.m	
Wire Stripping Length	10 mm	
Tool Type	Connection: screwdriver Disconnection: screwdriver	
[Ue] Rated Operational Voltage	1000 V conforming to EN/IEC 60947-7-1 600 V CSA 690 V conforming to ATEX Exe II Ex II 2 GD	

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

600 V cURus

10.0 cm

Package 2 Width

Package 2 Length	26.0 cm
Package 2 Weight	718.0 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	750
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	11.277 kg

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes
<b>⊘</b>	Halogen Free Plastic Parts Product	

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations