Product datasheet

Specifications





Harmony. Slim interface relay preassembled. 6 A. 1 CO. with LED. with protection circuit. spring terminals. 24 V AC/DC

RSL1PRBU

Price: 428.03 ZAR

Main

Range Of Product	Harmony Electromechanical Relays
Series Name	Interface relay
Product Or Component Type	Pre-assembled plug-in relay with socket
Device Short Name	RSL
Contacts Type And Composition	1 C/O
Contact Operation	Standard
[Uc] Control Circuit Voltage	24 V AC/DC
[Ithe] Conventional Enclosed Thermal Current	6 A at -4055 °C
Status Led	With
Shape Of Pin	Flat (PCB type)

Complementary

Complementary	
Fixing Mode	Plastic compression spring
Average Resistance	3390 Ohm network: DC at 23 °C +/- 10 %
[Ui] Rated Insulation Voltage	250 V conforming to IEC 277 V conforming to cUL
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC
Contacts Material	Silver alloy (AgSnO2)
[le] Rated Operational Current	6 A 1 C/O (AC-1/DC-1) conforming to IEC/UL
Minimum Switching Current	100 mA
Maximum Switching Voltage	277 V
Minimum Switching Voltage	12 V
Maximum Switching Capacity	1500 VA 150 W
Minimum Switching Capacity	120 mW
Operating Rate	<= 72000 cycles/hour no-load <= 360 cycles/hour under load
Mechanical Durability	10000000 cycles
Electrical Durability	60000 cycles for resistive load, 6 A at 250 V, AC-1
Operating Time	5 ms reset 12 ms
Marking	CE

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Protection Category	RT III
Test Levels	Level A group mounting
Operating Position	Any position
Height	78.6 mm
Width	6.2 mm
Depth	101 mm
Terminals Description Iso N°1	(A1-A2)CO (11-12-14)OC
Sale Per Indivisible Quantity	10
Net Weight	0.029 kg
Load Current	6 A at 250 V AC 0.5 mm mounting distance
Average Coil Consumption	0.17 W, DC
Drop-Out Voltage Threshold	>= 0.05 Uc
Contact Terminal Arrangement	Separate
Connections - Terminals	Spring terminals, 1 x 0.21 x 1.5 mm ² (AWG 24AWG 16) flexible with cable end Spring terminals, 1 x 0.21 x 1.5 mm ² (AWG 24AWG 16) solid without cable end
Safety Reliability Data	B10d = 60000
Clamping Force	1040 N
Control Type	Without push-button
Mounting Support	35 mm symmetrical DIN rail
Device Presentation	Complete product

Environment

Input Voltage	$24 \vee AC/DC$ (input voltage limit: $24 \in 29.8 \vee$)
	24 V AC/DC (input voltage limit: 21.628.8 V)
Dielectric Strength	1000 V AC between contacts
	4000 V AC between coil and contact
Standards	IEC 61810-1
	CSA C22.2 No 14
	UL 508
Product Certifications	UL
	CSA
	GOST
Ambient Air Temperature For Storage	-4085 °C
Vibration Resistance	10 gn, amplitude = +/- 1 mm (f = 10…150 Hz)10 cycles not operating conforming to IEC 60068-2-6
	5 gn, amplitude = +/- 1 mm (f = 10150 Hz)10 cycles in operation conforming to IEC 60068-2-6
Ip Degree Of Protection	IP40 conforming to IEC 60529
Shock Resistance	10 gn (duration = 11 ms) for in operation conforming to IEC 60068-2-27
	5 gn (duration = 11 ms) for not operating conforming to IEC 60068-2-27
Ambient Air Temperature For Operation	-4055 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.800 cm

Package 1 Width	8.000 cm
Package 1 Length	10.500 cm
Package 1 Weight	28 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	7.000 cm
Package 2 Width	8.800 cm
Package 2 Length	11.000 cm
Package 2 Weight	308 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	300
Package 3 Height	30.000 cm
Package 3 Width	30.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	9.782 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Toxic Free
Phenolic Free Solution

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Product datasheet

Dimensions Drawings

Dimensions

