Product datasheet

Specifications



APC Smart-UPS SRT, 1500VA, 230V, LCD, rackmount, w/kit, 6x, IEC, 60320, C13, outlets

SRT1500XLI

Overview	
Presentation	High density, double-conversion on-line power protection with scalable runtime.
Lead Time	Usually in Stock
Main	
Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	1500 W
Rated Power In Va	1500 VA
Input Connection Type	IEC 60320 C14
Output Connection Type	6 IEC 60320 C13
Cable Length	1.83 m
Number Of Cables	1
Provided Equipment	CD with software Communication cable Documentation CD Installation guide Removable support feet USB cable Warranty card

Batteries & Runtime

Run Time	View Runtime Graph
Battery Type	Lead-acid battery
Number Of Battery Filled Slots	1
Number Of Battery Free Slots	0
Battery Recharge Time	3 h
Number Of Battery Replacement Quantity	1
Battery Voltage	48 V
Battery Charger Power	108 W rated
Battery Life	35 year(s)
Replacement Battery	APCRBC155 🗗

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

General

Ups Туре	Double conversion online
Product Web Sub-Family	High density
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

Colour	Black
Height	43.2 cm
Width	8.5 cm
Depth	50.5 cm
Net Weight	20.5 kg
Mounting Preference	No preference
Mounting Mode	Rack-mounted with kit
Two Post Mountable	0
Usb Compatible	Yes
Mounting Position	Vertical

Input

Network Frequency	4070 Hz auto-sensing
Input Voltage Limits	100275 V

Output

-	
Maximum Configurable Power In Va	1500 VA
Maximum Configurable Power In W	1500 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Wave Type	Sine wave
Harmonic Distortion	Less than 2 %
Crest Factor	3 : 1
Bypass Type	Built-in bypass

Conformance

Product Certifications	CE EAC
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For 0...40 °C Operation

Relative Humidity	095 % non-condensing
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-2050 °C
Storage Relative Humidity	095 % non-condensing
Storage Altitude	0.0015240.00 m
Acoustic Level	50 dBA
Heat Dissipation	317 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	1
Alarm	Audible and visible alarms : prioritized by severity
Emergency Power Off	Yes

Surge Protection and Filtering

Surge Energy Rate

432 J

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.6 cm
Package 1 Width	74.9 cm
Package 1 Length	59.4 cm
Package 1 Weight	29.6 kg

Contractual warranty

Warranty

3 years repair or replace (excluding battery) and 2 years for battery

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information