

Product datasheet

Specifications



basic digital input kit STB - 24 V DC - 6 I

STBDDI3615K

Price: 1,314.04 ZAR

Main

Range Of Product	Modicon STB distributed I/O solution
Product Or Component Type	Basic digital input kit
Kit Composition	STBXTS1100, 6-terminal screw type connector STBDDI3615 module STBXBA1000 base STBXTS2100, 6-terminal spring clamp connector
Discrete Input Number	6
Discrete Input Voltage	24 V
Discrete Input Voltage Type	DC

Complementary

Input Voltage Limits	15...30 V at state 1 -3...5 V at state 0
Permissible Voltage	30 V
Absolute Maximum Voltage	56 V 1.3 ms
Discrete Input Current	4.5 mA
Current State 0 Guaranteed	<= 0.5 mA
Current State 1 Guaranteed	>= 2.5 mA
Discrete Input Logic	Positive
Response Time	5.25 ms off-to-on 5.75 ms on-to-off
Protection Type	Power protection integrated fuse on PDM time lag 5 A Input protection resistor-limited Reverse polarity protection
Insulation Between Channels And Logic Bus	1500 V for 1 minute
Cold Swapping	Yes
Hot Swapping	Yes for basic NIMs
Input Filtering	5 ms
Product Compatibility	Power distribution module STBPDT3100/3105 I/O base STBXBA1000
[Us] Rated Supply Voltage	24 V DC
Supply	Power distribution module
Current Consumption	45 mA at 5 V DC for logic bus
Marking	CE
Overvoltage Category	II

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Status Led	1 LED (green) module status (RDY) 1 LED per channel (green) channel status (IN1 to IN6)
Depth	65.1 mm
Height	18.4 mm
Width	125 mm
Net Weight	0.112 kg

Environment

Standards	EN/IEC 61131-2 type 1
Product Certifications	UL FM Class 1 Division 2 CSA
Pollution Degree	2 conforming to IEC 60664-1
Operating Altitude	<= 2000 m
Ip Degree Of Protection	IP20 conforming to IEC 61131-2 class 1
Ambient Air Temperature For Operation	0...60 °C (without derating)
Ambient Air Temperature For Operation	32...140 °F without derating
Ambient Air Temperature For Storage	-40...85 °C without derating
Ambient Air Temperature For Storage	-40...185 °F without derating
Relative Humidity	95 % at 60 °C without condensation
Vibration Resistance	3 gn at 58...150 Hz on 35 x 7.5 mm symmetrical DIN rail 5 gn at 58...150 Hz on 35 x 15 mm symmetrical DIN rail +/-0.35 mm at 10...58 Hz
Shock Resistance	30 gn for 11 ms conforming to IEC 88 reference 2-27

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	8.0 cm
Package 1 Length	13.0 cm
Package 1 Weight	134.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	28
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	4.178 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	448
Package 3 Height	60.0 cm
Package 3 Width	80.0 cm
Package 3 Length	448.0 cm

Package 3 Weight	60.032 kg
------------------	-----------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)


[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Dimensions Drawings

Dimensions




Connections and Schema

Wiring Diagram

Example

6 two-wire sensors



Pin	Top Connector	Bottom Connector
1	+24 VDC sensor bus power	+24 VDC sensor bus power
2	input from sensor 1	input from sensor 4
3	+24 VDC sensor bus power	+24 VDC sensor bus power
4	input from sensor 2	input from sensor 5
5	+24 VDC sensor bus power	+24 VDC sensor bus power
6	input from sensor 3	input from sensor 6