

Product datasheet

Specifications



TSX Micro - 4 analogue output +/- 10 V, 0-10 V

TSXASZ401

⚠ Discontinued on: 23 Jul 2021

⚠ To be end-of-service on: 31 Dec 2027

⚠ To be discontinued

Price: 11,377.66 ZAR

Main

Range Of Product	Modicon TSX Micro automation platform
Product Or Component Type	Analog output module
Number Of Channels	4
Analogue Output Type	+/- 10 V 0...10 V

Complementary

Analogue/Digital Conversion	11 bits 0...10 V 11 bits + sign +/- 10 V
Response Time	400 µs
Output Load	>= 2 Ohm
Protection Type	Short-circuit
Temperature Drift	0.096 %/10 °C
Current Consumption	90 mA
Isolation Voltage	1000 V AC
Net Weight	0.2 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	18.0 cm
Package 1 Length	26.0 cm
Package 1 Weight	636.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	8
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.088 kg

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Connections and Schema

Wiring Diagram

