

Product datasheet

Specifications



double-format PL7 processor - 550 mA 5 V DC

TSXP57203M

⚠ Discontinued on: 31 Dec 2018

⚠ To be end-of-service on: 31 Dec 2026

⚠ Discontinued - Service only

Price: 40,381.24 ZAR

Main

Range Of Product	Modicon Premium Automation platform
Product Or Component Type	Double-format PL7 processor
Software Designation	PL7 Junior/Pro

Complementary

Number Of Racks	16 4/6/8 slots 8 12 slots
Number Of Slots	96 64 128
Discrete I/O Processor Capacity	1024 I/O
Analogue I/O Processor Capacity	80 I/O
Number Of Application Specific Channel	24
Number Of Process Control Channel	10 up to 30 simple loops
Integrated Connection Type	Non isolated serial link 2 female mini DIN connector (19.2 kbit/s)
Communication Module Processor Capacity	1 fieldbus module (none if CANopen used) 1 network module 4 AS-Interface bus modules 1 CANopen
Memory Description	Internal RAM (with PCMCIA card) 48 Kwords data Internal RAM (without PCMCIA card) 48 Kwords program and data PCMCIA card 160 Kwords program PCMCIA card 2688 Kwords additional data storage
Maximum Size Of Object Areas	30.5 %MWi internal words located internal data 32 %KWi constant words located internal data 8132 %Mi located internal bits
Application Structure	1 fast task 1 master task 64 event tasks
Execution Time Per Instruction	0.19 µs Boolean without PCMCIA card 0.21 µs Boolean with PCMCIA card 0.25 µs word or fixed-point arithmetic without PCMCIA card 0.42 µs word or fixed-point arithmetic with PCMCIA card 2.6 µs floating points with PCMCIA card 2.6 µs floating points without PCMCIA card
Number Of Instructions Per Ms	2.5 Kinst/ms 65 % Boolean + 35 % fixed arithmetic with PCMCIA card 3.57 Kinst/ms 65 % Boolean + 35 % fixed arithmetic without PCMCIA card 3.7 Kinst/ms 100 % Boolean with PCMCIA card 4.76 Kinst/ms 100 % Boolean without PCMCIA card

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

System Overhead	0.35 ms for fast task 1 ms for master task
Marking	CE
Local Signalling	1 LED (green) for processor running (RUN) 1 LED (red) for I/O module or configuration fault (I/O) 1 LED (red) for processor or system fault (ERR) 1 LED (yellow) for activity on the terminal port (TER)
Current Consumption	750 mA at 5 V DC
Module Format	Double
Net Weight	0.52 kg

Environment

Standards	CSA C22.2 No 142 UL 508 CSA C22.2 No 213 Class I Division 2 Group A IEC 61131-2 89/336/EEC 73/23/EEC CSA C22.2 No 213 Class I Division 2 Group C 92/31/EEC CSA C22.2 No 213 Class I Division 2 Group B 93/68/EEC CSA C22.2 No 213 Class I Division 2 Group D
Product Certifications	LR DNV RMRS GL RINA BV ABS
Ambient Air Temperature For Operation	0...60 °C
Ambient Air Temperature For Storage	-25...70 °C
Relative Humidity	10...95 % without condensation for operation 5...95 % without condensation for storage
Operating Altitude	0...2000 m
Protective Treatment	TC
Ip Degree Of Protection	IP20
Pollution Degree	2

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.5 cm
Package 1 Width	18.0 cm
Package 1 Length	26.0 cm
Package 1 Weight	646.0 g
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.0 cm
Package 2 Width	40.0 cm
Package 2 Length	60.0 cm

Package 2 Weight	4.823 kg
------------------	----------


Contractual warranty

Warranty	18 months
----------	-----------

Dimensions Drawings

Standard and Extendable Racks for Modules Mounting

Dimensions of Modules and Racks



- (1) With screw terminal block modules.
- (2) Maximum depth for all types of modules and their associated connectors.