Product datasheet

Specifications





VarSet capacitor bank Auto 016kvar with incomer CB xxB 400V 50Hz

VLVAW0N03502AA

Price: 54,469.20 ZAR

Main

Network Rated Voltage	400 V AC 50 Hz 415 V AC 50 Hz
Reactive Power Rating	16 kvar
Operating Mode	Automatic
Range	PowerLogic
Device Short Name	automatic capacitor bank
Product Or Component Type	Capacitor bank

Complementary

Complementary	
Network Pollution Level	Low polluted
[Gh/Sn] Harmonic Pollution Rate	1525 %
[Thdu] Total Harmonic Distorsion Of Voltage	34 %
Power Per Step	3 kvar
Step Composition	3 + 2x6.25
Location Of Connection	Bottom
Controller Type	PowerLogic PFC Controller VPL6
Capacitor Technology	PowerLogic PFC Capacitor
Poles Description	3P
Capacitance Tolerance	- 5 % to 10 %
[Ui] Rated Insulation Voltage	500 V
[Uimp] Rated Impulse Withstand Voltage	6 kV
Maximum Permissible Voltage	1.1 x Un (8 hours over 24 hours) conforming to IEC 60831
[Imp] Maximum Permanent Current	Capacitor: 1.8 x In at 480 V conforming to IEC 60831 Battery: 1.43 x In at 400 V conforming to IEC 61439-2 Battery: 1.19 x In at 415 V conforming to IEC 61439-2
Main Incomer Protection	Circuit breaker protection
Breaking Capacity	lcu 15 kA
Step Protection Type	Overload: harmonic control from PowerLogic PFC Controller Short-circuit: main circuit breaker
Accessibility For Operation	Front
Colour	Grey (RAL 7035)
Maximum Weight	57 kg
Height	650 mm

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Width	450 mm
Depth	250 mm
Provided Equipment	Auxiliary transformer
Internal Voltage Transformer	400/230 V - 100 VA
Function Available	Alarm contact GenSet shedding contact

Environment

Standards	IEC 61439-1 IEC 61921
	IEC 61439-2
Product Certifications	CE EAC
	ASEFA
Mounting Location	Indoor
Ip Degree Of Protection	Environment: IP31 Safety: IPxx B
Ik Degree Of Protection	IK10
Relative Humidity	095 %
Operating Altitude	<= 2000 m
Ambient Air Temperature For Operation	-545 °C
Average Ambient Air Temperature For Operation	35 °C (annual) 45 °C (over 24 hours)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	82.000 cm
Package 1 Width	60.000 cm
Package 1 Length	80.000 cm
Package 1 Weight	47.000 kg

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins