# **Product datasheet**

Specifications





! Discontinued

Harmony XAP, XB2 SL, Empty control station, zinc alloy, yellow lid, blue base, 1 cut-out, Ø22, 80 x 80 x 51.5 mm

XAPJ1201

- ! Discontinued on: 14 Oct 2022
- ! End-of-service on: 31 Oct 2023

#### Main

Range Of Product	Harmony XAP						
Product Or Component Type	Die-cast empty control station						
Device Short Name	XAPJ						
Product Destination	For Ø 22 mm control and signalling units						
Product Front Plate Size	80 x 80 mm						
Usable Depth	49 mm						
Number Of Cut-Out	1 cut-out						
Colour Of Base Of Enclosure	Blue						
Colour Of Cover	Yellow						
Material	Zinc alloy						
Cable Entry	1 hole with blanking plug for cable gland, clamping capacity: 14 mm 1 hole without blanking plug for cable gland, clamping capacity: 14 mm						
Device Mounting	Flush						
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP69 conforming to NF C 20-010 IP69K						

## Complementary

Number Of Vertical Rows	1
Net Weight	0.455 kg

## **Environment**

Protective Treatment	TC		
Ambient Air Temperature For Storage	-4070 °C		
Ambient Air Temperature For Operation	-4070 °C		
Overvoltage Category	Class I conforming to IEC 60536 Class I conforming to NF C 20-030		

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	4

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Package 1 Height	9.5 cm		
Package 1 Width	10 cm		
Package 1 Length	10 cm		
Package 1 Weight	529 a		

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance

<b>⊘</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>9</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes


## **Certifications & Standards**

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				

#### **Dimensions Drawings**

#### **Dimensions and Fixing**

Refer to the product characteristics to get the number of cut-outs.



- (1) 1 hole, without blanking plug, for cable gland with 14 mm/0.55 in. maximum clamping capacity
- (2) 1 hole, with blanking plug (protrusion 6 mm/0.23 in.), for cable gland with 14 mm/0.55 in. maximum clamping capacity
- (3)  $2 \times \emptyset$  5.6 mm/0.22 in. holes, depth 20 mm/0.78 in.

#### P Usable depth

а		b		С		G		Н		Р	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	80	3.15	51.5	2.01	50	1.97	65	2.56	49	1.93