# **Product datasheet**

Specifications





Harmony XB4. Single contact block with body/fixing collar. metal. spring clamp terminal. 1 NC

ZB4BZ1025

Price: 193.48 ZAR

#### Main

Range Of Product	Harmony XB4	
Product Or Component Type	Complete body/contact assembly	
Device Short Name	ZB4	
Fixing Collar Material	Zamak	
Sale Per Indivisible Quantity	1	
Head Type	Standard	
Contacts Type And Composition	1 NC	
Contact Operation	Slow-break	
Contact Block Type	Single	
Device Composition	Body Fixing collar	
Connections - Terminals	Spring clamp terminals	

## Complementary

Cad Overall Width	46.2 mm	
Cad Overall Height	27.6 mm	
Cad Overall Depth	30 mm	
Terminals Description Iso N°1	(11-12)NC	
Net Weight	0.049 kg	
Contacts Usage	Standard contacts	
Positive Opening	With conforming to IEC 60947-5-1 appendix K	
Operating Travel	1.5 mm (NC changing electrical state) 4.3 mm (total travel)	
Operating Force	2 N NC changing electrical state	
Mechanical Durability	10000000 cycles	
Contacts Material	Silver alloy (Ag/Ni)	
Electrical Durability	urability 10000000 cycles	
Device Presentation	Basic sub-assemblies	

#### **Environment**

Protective Treatment	тн
Ambient Air Temperature For Storage	-4070 °C

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Ambient Air Temperature For Operation	-4070 °C	
Ip Degree Of Protection	IP20 conforming to IEC 60529	
Standards	CSA C22.2 No 14 IEC 60947-5-1 IEC 60947-5-4 IEC 60947-5-5 JIS C8201-5-1 IEC 60947-1 UL 508 JIS C8201-1	
Product Certifications	GL BV DNV CSA LROS (Lloyds register of shipping) UL	
Vibration Resistance	5 gn (f= 2500 Hz) conforming to IEC 60068-2-6	
Shock Resistance	30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27	

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.300 cm
Package 1 Width	3.400 cm
Package 1 Length	5.200 cm
Package 1 Weight	52.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	200
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	10.876 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	1600
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	97.404 kg

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance


<b>Ø</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

### **Dimensions Drawings**

#### **Dimensions**



### ZB4BZ1025

#### Mounting and Clearance


# Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connectors or on Printed Circuit Board

(1)

(2)

Connection by Screw Clamp Terminals or Plug-in



**Connection by Faston Connectors** 

(1) Diameter on finished panel or support

(3)

- (2) 40 mm min. / 1.57 in. min.
- (3) 30 mm min. / 1.18 in. min.
- (4) Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm  $_0^{+0.4}$  / 0.88 in.  $_0^{+0.016}$ )

(4)

- (5) 45 mm min. / 1.78 in. min.
- (6) 32 mm min. / 1.26 in. min.