# **Product datasheet**

Specification





# controller M221 16 IO transistor PNP

TM221C16T

## Main

Range Of Product	Modicon M221
Product Or Component Type	Logic controller
[Us] Rated Supply Voltage	24 V DC
Discrete Input Number	9, discrete input 4 fast input conforming to IEC 61131-2 Type 1
Analogue Input Number	2 at 010 V
Discrete Output Type	Transistor
Discrete Output Number	7 transistor 2 fast output
Discrete Output Voltage	24 V DC
Discrete Output Current	0.5 A

# Complementary

•	
Discrete I/O Number	16
Maximum Number Of I/O Expansion Module	4 (local I/O-Architecture) 11 (remote I/O-Architecture)
Supply Voltage Limits	20.428.8 V
Inrush Current	35 A
Maximum Power Consumption In W	10 W at 24 V (with max number of I/O expansion module) 3.9 W at 24 V (without I/O expansion module)
Power Supply Output Current	0.325 A 5 V for expansion bus 0.15 A 24 V for expansion bus
Discrete Input Logic	Sink or source (positive/negative)
Discrete Input Voltage	24 V
Discrete Input Voltage Type	DC
Analogue Input Resolution	10 bits
Lsb Value	10 mV
Conversion Time	1 ms per channel + 1 controller cycle time for analogue input analog input
Permitted Overload On Inputs	+/- 30 V DC for 5 min (maximum) for analog input +/- 13 V DC (permanent) for analog input
Voltage State 1 Guaranteed	>= 15 V for input
Voltage State 0 Guaranteed	<= 5 V for input
Discrete Input Current	7 mA for discrete input 5 mA for fast input
Input Impedance	3.4 kOhm for discrete input 100 kOhm for analog input 4.9 kOhm for fast input

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Response Time	35 µs turn-off, 1215 terminal(s) for input 5 µs turn-on, 10, 11, 16, 17 terminal(s) for fast input 35 µs turn-on, other terminals terminal(s) for input 5 µs turn-off, 10, 11, 16, 17 terminal(s) for fast input 100 µs turn-off, other terminals terminal(s) for input 5 µs turn-on, turn-off, Q0Q1 terminal(s) for output 50 µs turn-on, turn-off, Q2Q3 terminal(s) for output 300 µs turn-on, turn-off, other terminals terminal(s) for output	
Configurable Filtering Time	0 ms for input 3 ms for input 12 ms for input	
Discrete Output Logic	Positive logic (source)	
Maximum Current Per Output Common	3.5 A	
Output Frequency	100 kHz for fast output (PWM/PLS mode) at Q0Q1 5 kHz for output at Q2Q3 0.1 kHz for output at Q4Q6	
Absolute Accuracy Error	+/- 1 % of full scale for analog input	
Maximum Leakage Current	0.1 mA for transistor output	
Maximum Voltage Drop	<1 V	
Mechanical Durability	20000000 cycles for transistor output	
Maximum Tungsten Load	<12 W for output and fast output	
Protection Type	Overload and short-circuit protection at 0.2 A	
Reset Time	1 s automatic reset	
Memory Capacity	256 kB for user application and data RAM with 10000 instructions 256 kB for internal variables RAM	
Data Backed Up	256 kB built-in flash memory for backup of application and data	
Data Storage Equipment	2 GB SD card (optional)	
Battery Type	BR2032 or CR2032X lithium non-rechargeable	
Backup Time	1 year at 25 °C (by interruption of power supply)	
Execution Time For 1 Kinstruction	0.3 ms for event and periodic task	
Execution Time Per Instruction	0.2 μs Boolean	
Exct Time For Event Task	60 μs response time	
Maximum Size Of Object Areas	512 %KW constant words 512 %M memory bits 255 %TM timers 8000 %MW memory words 255 %C counters	
Realtime Clock	With	
Clock Drift	<= 30 s/month at 25 °C	
Regulation Loop	Adjustable PID regulator up to 14 simultaneous loops	
Positioning Functions	Position PTO 2 axe(s)pulse/direction mode (100 kHz) Position PTO 1 axe(s)CW/CCW mode (100 kHz)	
Function Available	Frequency generator PWM PLS	
Counting Input Number	4 fast input (HSC mode) at 100 kHz 32 bits	
Counter Function	Pulse/direction A/B Single phase	
Integrated Connection Type	USB port with mini B USB 2.0 connector  Non isolated serial link serial 1 with RJ45 connector and RS485 interface  Non isolated serial link serial 2 with RJ45 connector and RS232/RS485 interface	

(serial)serial link supply: 5 V, <200 mA	
1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 480 Mbit/s for USB	
USB port: USB - SoMachine-Network Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network	
1 LED (green) for PWR 1 LED (green) for RUN 1 LED (red) for module error (ERR) 1 LED (green) for SD card access (SD) 1 LED (red) for BAT 1 LED (green) for SL1 1 LED (green) for SL2 1 LED per channel (green) for I/O state	
removable screw terminal block for inputs removable screw terminal block for outputs terminal block, 3 terminal(s) for connecting the 24 V DC power supply connector, 4 terminal(s) for analogue inputs Mini B USB 2.0 connector for a programming terminal	
Shielded cable: <10 m for fast input Unshielded cable: <30 m for output Unshielded cable: <30 m for digital input Unshielded cable: <1 m for analog input Shielded cable: <3 m for fast output	
Between input and internal logic at 500 V AC Non-insulated between inputs Between output and internal logic at 500 V AC Non-insulated between analogue input and internal logic Non-insulated between analogue inputs Between supply and ground at 1500 V AC Between input and ground at 500 V AC Between supply and internal logic at 2300 V AC	
CE	
Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit	
90 mm	
70 mm	
95 mm	
0.346 kg	
IEC 61131-2 UL 508 CAN/CSA C22.2 No. 213 IACS E10 ANSI/ISA 12-12-01	
RCM LR cULus ABS EAC DNV-GL	
CE UKCA cULus HazLoc	

8 kV in air conforming to IEC 61000-4-2 4 kV on contact conforming to IEC 61000-4-2

Resistance To Electrostatic Discharge

Resistance To Electromagnetic Fields	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3
. 16140	3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3 1 V/m 22.7 GHz conforming to IEC 61000-4-3
Resistance To Magnetic Fields	30 A/m 50/60 Hz conforming to IEC 61000-4-8
Resistance To Fast Transients	2 kV (power lines) conforming to IEC 61000-4-4
	2 kV (relay output) conforming to IEC 61000-4-4
	1 kV (I/O) conforming to IEC 61000-4-4
	1 kV (Ethernet line) conforming to IEC 61000-4-4 1 kV (serial link) conforming to IEC 61000-4-4
Commo Mithesterral	
Surge Withstand	2 kV power lines (AC) common mode conforming to IEC 61000-4-5 2 kV relay output common mode conforming to IEC 61000-4-5
	1 kV I/O common mode conforming to IEC 61000-4-5
	1 kV shielded cable common mode conforming to IEC 61000-4-5
	0.5 kV power lines (DC) differential mode conforming to IEC 61000-4-5
	1 kV power lines (AC) differential mode conforming to IEC 61000-4-5
	1 kV relay output differential mode conforming to IEC 61000-4-5
	0.5 kV power lines (DC) common mode conforming to IEC 61000-4-5
Resistance To Conducted Disturbances	10 V 0.1580 MHz conforming to IEC 61000-4-6
Distuibances	3 V 0.180 MHz conforming to Marine specification (LR, ABS, DNV, GL)
	10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to Marine specification (LR, ABS, DNV, GL)
Electromagnetic Emission	
Electromagnetic Emission	Conducted emissions - test level: 79 dBµV/m QP/66 dBµV/m AV ( power lines (AC)) at 0.150.5 MHz conforming to IEC 55011
	Conducted emissions - test level: 73 dBµV/m QP/60 dBµV/m AV ( power lines (AC))
	at 0.5300 MHz conforming to IEC 55011
	Conducted emissions - test level: 12069 dB $\mu$ V/m QP ( power lines) at 10150 kHz
	conforming to IEC 55011
	Conducted emissions - test level: 63 dBµV/m QP ( power lines) at 1.530 MHz
	conforming to IEC 55011  Radiated emissions - test level: 40 dBµV/m QP class A ( 10 m) at 30230 MHz
	conforming to IEC 55011
	Conducted emissions - test level: 7963 dBµV/m QP ( power lines) at 1501500
	kHz conforming to IEC 55011
	Radiated emissions - test level: 47 dBµV/m QP class A ( 10 m) at 2001000 MHz
	conforming to IEC 55011
Immunity To Microbreaks	10 ms
Ambient Air Temperature For Operation	-1055 °C (horizontal installation) -1035 °C (vertical installation)
Ambient Air Temperature For Storage	-2570 °C
Relative Humidity	1095 %, without condensation (in operation)
Notative Fullidity	1095 %, without condensation (in operation)
lp Degree Of Protection	IP20 with protective cover in place
Pollution Degree	<= 2
Operating Altitude	02000 m
Storage Altitude	03000 m
Vibration Resistance	3.5 mm at 58.4 Hz on symmetrical rail
	3.5 mm at 58.4 Hz on panel mounting
	1 gn at 8.4150 Hz on symmetrical rail
	1 gn at 8.4150 Hz on panel mounting
Shock Resistance	147 m/s² for 11 ms
Packing Units	
	DCE
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.129 cm
Package 1 Width	14.031 cm
Package 1 Length	14.163 cm

Package 1 Weight	551.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	28.8 cm
Package 2 Width	39.1 cm
Package 2 Length	56.6 cm
Package 2 Weight	11.98 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	240
Package 3 Height	105.0 cm
Package 3 Width	120.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	150 kg



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance

<b>②</b>	Mercury Free	
	Rohs Exemption Information	Yes
	Pvc Free	

#### **Certifications & Standards**


Circularity Profile	End of Life Information	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Environmental Disclosure	Product Environmental Profile	
China Rohs Regulation	China RoHS declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
Reach Regulation	REACh Declaration	


# **Product datasheet**

# TM221C16T

**Dimensions Drawings** 


#### **Dimensions**






Mounting and Clearance

Mounting on a Rail





#### **Direct Mounting on a Panel Surface**



(1) Install a mounting strip


#### **Mounting Hole Layout**






#### **Mounting**

#### **Correct Mounting Position**




#### **Acceptable Mounting Position**




#### **Incorrect Mounting Position**









#### Clearance





#### Connections and Schema

#### **Digital Inputs**




- (\*) Type T fuse
- (A) Sink wiring (positive logic).
- (B) Source wiring (negative logic).

#### **Connection of the Fast Inputs**




10, 11, 16, 17

#### **Transistor Outputs**




(\*) Type T fuse


#### **Connection of the Fast Outputs**



Q0, Q1

#### **Analog Inputs**







The (-) poles are connected internally.

Pin	Wire Color
0 V	Black
AN1	Red
0 V	Black
AN0	Red

#### **USB Mini-B Connection**



#### **SL1 Connection**




SL1


Ν°	RS 232	RS 485
1	RxD	N.C.
2	TxD	N.C.
3	RTS	N.C.
4	N.C.	D1
5	N.C.	D0
6	стѕ	N.C.
7	N.C*.	5 Vdc
8	Common	Common

N.C.: not connected

 $<sup>\</sup>ensuremath{^*}$  : 5 Vdc delivered by the controller. Do not connect.



#### **SL2 Connection**




Ν°	RS 485
1	N.C.
2	N.C.
3	N.C.
4	D1
5	D0
6	N.C.
7	N.C.
8	Common

N.C.: not connected

#### Performance Curves

#### **Derating Curves**


#### **Embedded Digital Inputs (No Cartridge)**



X: Ambient temperature

Y: Input simultaneous ON ratio

## **Embedded Digital Inputs (with Cartridge)**




X: Ambient temperature

Y: Input simultaneous ON ratio

#### **Derating Curves**


#### **Embedded Digital Outputs (No Cartridge)**



X: Ambient temperature

Y: Output simultaneous ON ratio

#### **Embedded Digital Outputs (with Cartridge)**



X: Ambient temperature

Y: Output simultaneous ON ratio