Product datasheet

Specification





controller M221 24 IO transistor PNP Ethernet

TM221CE24T

Main

Range Of Product	Modicon M221	
Product Or Component Type	Logic controller	
[Us] Rated Supply Voltage	24 V DC	
Discrete Input Number	14, discrete input 4 fast input conforming to IEC 61131-2 Type 1	
Analogue Input Number	2 at 010 V	
Discrete Output Type	Transistor	
Discrete Output Number	10 transistor 2 fast output	
Discrete Output Voltage	24 V DC	
Discrete Output Current	0.5 A	

Complementary

Discrete I/O Number	24	
Maximum Number Of I/O Expansion Module	7 (local I/O-Architecture) 14 (remote I/O-Architecture)	
Supply Voltage Limits	20.428.8 V	
Inrush Current	35 A	
Maximum Power Consumption In W	14 W at 24 V (with max number of I/O expansion module) 4.8 W at 24 V (without I/O expansion module)	
Power Supply Output Current	0.52 A 5 V for expansion bus 0.2 A 24 V for expansion bus	
Discrete Input Logic Sink or source (positive/negative)		
Discrete Input Voltage	24 V	
Discrete Input Voltage Type	DC	
Analogue Input Resolution	10 bits	
Lsb Value	10 mV	
Conversion Time	1 ms per channel + 1 controller cycle time for analogue input analog input	
Permitted Overload On Inputs	+/- 30 V DC for 5 min (maximum) for analog input +/- 13 V DC (permanent) for analog input	
Voltage State 1 Guaranteed	>= 15 V for input	
Voltage State 0 Guaranteed <= 5 V for input		
Discrete Input Current 7 mA for discrete input 5 mA for fast input		
Input Impedance	3.4 kOhm for discrete input 100 kOhm for analog input 4.9 kOhm for fast input	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

35 μs turn-off, I2I5 terminal(s) for input	
5 µs turn-on, I0, I1, I6, I7 terminal(s) for fast input	
35 μs turn-on, other terminals terminal(s) for input 5 μs turn-off, I0, I1, I6, I7 terminal(s) for fast input	
100 µs turn-off, other terminals terminal(s) for input	
5 µs turn-on, turn-off, Q0Q1 terminal(s) for output	
50 μs turn-on, turn-off, Q2Q3 terminal(s) for output	
300 µs turn-on, turn-off, other terminals terminal(s) for output	
0 ms for input	
3 ms for input	
12 ms for input	
Positive logic (source)	
Per Output 5 A	
100 kHz for fast output (PWM/PLS mode) at Q0Q1	
5 kHz for output at Q2Q3	
0.1 kHz for output at Q4Q9	
+/- 1 % of full scale for analog input	
0.1 mA for transistor output	
<1 V	
20000000 cycles for transistor output	
<12 W for output and fast output	
Overload and short-circuit protection at 1 A	
<u> </u>	
1 s automatic reset	
256 kB for user application and data RAM with 10000 instructions 256 kB for internal variables RAM	
256 kB built-in flash memory for backup of application and data	
2 GB SD card (optional)	
BR2032 or CR2032X lithium non-rechargeable	
1 year at 25 °C (by interruption of power supply)	
n 0.3 ms for event and periodic task	
n Time Per Instruction 0.2 μs Boolean	
60 μs response time	
255 %C counters	
512 %M memory bits	
8000 %MW memory words	
512 %KW constant words 255 %TM timers	
With	
<= 30 s/month at 25 °C	
Adjustable PID regulator up to 14 simultaneous loops	
Position PTO 2 axe(s)pulse/direction mode (100 kHz) Position PTO 1 axe(s)CW/CCW mode (100 kHz)	
Frequency generator	
PLS	
PWM	
4 fast input (HSC mode) at 100 kHz 32 bits	
A/B	
Single phase Pulse/direction	
USB port with mini B USB 2.0 connector Non isolated serial link serial 1 with RJ45 connector and RS232/RS485 interface Ethernet with RJ45 connector	

Supply (serial)serial link supply: 5 V, <200 mA		
Transmission Rate	1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 480 Mbit/s for USB	
Communication Port Protocol	USB port: USB - SoMachine-Network Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network Ethernet	
Port Ethernet	10BASE-T/100BASE-TX 1 port with 100 m copper cable	
Communication Service	Modbus TCP slave device Modbus TCP server Modbus TCP client Ethernet/IP adapter DHCP client	
Local Signalling	1 LED (green) for PWR 1 LED (green) for RUN 1 LED (red) for module error (ERR) 1 LED (green) for SD card access (SD) 1 LED (red) for BAT 1 LED per channel (green) for I/O state 1 LED (green) for SL Ethernet network activity (green) for ACT Ethernet network link (yellow) for Link (Link Status)	
Electrical Connection	removable screw terminal block for inputs removable screw terminal block for outputs terminal block, 3 terminal(s) for connecting the 24 V DC power supply connector, 4 terminal(s) for analogue inputs Mini B USB 2.0 connector for a programming terminal	
Maximum Cable Distance Between Devices	Shielded cable: <10 m for fast input Unshielded cable: <30 m for output Unshielded cable: <30 m for digital input Unshielded cable: <1 m for analog input Shielded cable: <3 m for fast output	
nsulation	Between input and internal logic at 500 V AC Between fast input and internal logic at 500 V AC Non-insulated between inputs Between output and internal logic at 500 V AC Non-insulated between analogue input and internal logic Non-insulated between analogue inputs	
Marking	CE	
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit	
Height	90 mm	
Depth	70 mm	
Vidth	110 mm	
Net Weight	0.395 kg	
Environment		
Standards	IEC 61131-2 UL 508 CAN/CSA C22.2 No. 213 IACS E10	

Standards	IEC 61131-2 UL 508 CAN/CSA C22.2 No. 213 IACS E10
	ANSI/ISA 12-12-01
Product Certifications	ABS
	EAC
	RCM
	cULus
	LR
	DNV-GL
	CE
	UKCA
	cULus HazLoc

Environmental Characteristic	Ordinary and hazardous location
Resistance To Electrostatic	8 kV in air conforming to IEC 61000-4-2
Discharge	4 kV on contact conforming to IEC 61000-4-2
Resistance To Electromagnetic	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3
Fields	3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3
	1 V/m 22.7 GHz conforming to IEC 61000-4-3
Resistance To Magnetic Fields	30 A/m 50/60 Hz conforming to IEC 61000-4-8
Resistance To Fast Transients	2 kV (power lines) conforming to IEC 61000-4-4
	2 kV (relay output) conforming to IEC 61000-4-4
	1 kV (I/O) conforming to IEC 61000-4-4
	1 kV (Ethernet line) conforming to IEC 61000-4-4
	1 kV (serial link) conforming to IEC 61000-4-4
Surge Withstand	2 kV power lines (AC) common mode conforming to IEC 61000-4-5
	2 kV relay output common mode conforming to IEC 61000-4-5
	1 kV I/O common mode conforming to IEC 61000-4-5
	1 kV shielded cable common mode conforming to IEC 61000-4-5
	0.5 kV power lines (DC) differential mode conforming to IEC 61000-4-5
	1 kV power lines (AC) differential mode conforming to IEC 61000-4-5
	1 kV relay output differential mode conforming to IEC 61000-4-5
	0.5 kV power lines (DC) common mode conforming to IEC 61000-4-5
Resistance To Conducted	10 V 0.1580 MHz conforming to IEC 61000-4-6
Disturbances	3 V 0.180 MHz conforming to Marine specification (LR, ABS, DNV, GL)
	10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to
	Marine specification (LR, ABS, DNV, GL)
Electromagnetic Emission	Conducted emissions - test level: 79 dBµV/m QP/66 dBµV/m AV (power lines (AC))
_	at 0.150.5 MHz conforming to IEC 55011
	Conducted emissions - test level: 73 dBµV/m QP/60 dBµV/m AV (power lines (AC))
	at 0.5300 MHz conforming to IEC 55011
	Conducted emissions - test level: 12069 dBµV/m QP (power lines) at 10150 kHz
	conforming to IEC 55011
	Conducted emissions - test level: 63 dBµV/m QP (power lines) at 1.530 MHz
	conforming to IEC 55011
	Radiated emissions - test level: 40 dBµV/m QP class A (10 m) at 30230 MHz
	conforming to IEC 55011
	Conducted emissions - test level: 7963 dBµV/m QP (power lines) at 1501500
	kHz conforming to IEC 55011
	Radiated emissions - test level: 47 dBµV/m QP class A (10 m) at 2001000 MHz
	conforming to IEC 55011
mmunity To Microbreaks	10 ms
Ambient Air Temperature For	-1055 °C (horizontal installation)
Operation	-1035 °C (vertical installation)
Ambient Air Temperature For	-2570 °C
Storage	
Relative Humidity	1095 %, without condensation (in operation)
	1095 %, without condensation (in storage)
p Degree Of Protection	IP20 with protective cover in place
Pollution Degree	<= 2
Operating Altitude	02000 m
Storage Altitude	03000 m
Vibration Resistance	3.5 mm at 58.4 Hz on symmetrical rail
	3.5 mm at 58.4 Hz on panel mounting
	1 gn at 8.4150 Hz on symmetrical rail
	1 gn at 8.4150 Hz on panel mounting
Shock Resistance	147 m/s² for 11 ms
Packing Units	
Unit Type Of Package 1	DCE

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.133 cm

Package 1 Width	14.136 cm
Package 1 Length	15.607 cm
Package 1 Weight	621.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	29.7 cm
Package 2 Width	39.8 cm
Package 2 Length	57.0 cm
Package 2 Weight	13.211 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	240
Package 3 Height	105.0 cm
Package 3 Width	120.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	94 kg



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
②	Rohs Exemption Information	Yes
	Pvc Free	

Certifications & Standards


Circularity Profile	End of Life Information	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Environmental Disclosure	Product Environmental Profile	
China Rohs Regulation	China RoHS declaration	
Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)		
Reach Regulation	REACh Declaration	


Product datasheet

TM221CE24T

Dimensions Drawings

Dimensions







TM221CE24T

Mounting and Clearance

Mounting on a Rail





Direct Mounting on a Panel Surface



(1) Install a mounting strip


Mounting Hole Layout






Mounting

Correct Mounting Position




Acceptable Mounting Position




Incorrect Mounting Position









Clearance





Connections and Schema

Digital Inputs




- (*) Type T fuse
- (A) Sink wiring (positive logic).
- (B) Source wiring (negative logic).

Connection of the Fast Inputs



10, 11, 16, 17

Transistor Outputs




- (*) Type T fuse
- (1) The V+ terminals are connected internally.


Connection of the Fast Outputs



Q0, Q1

Analog Inputs






The (-) poles are connected internally.

Pin	Wire Color
0 V	Black
AN1	Red
0 V	Black
AN0	Red


Ethernet Connection




Pin N°	Signal
1	TD+
2	TD-
3	RD+
4	-
5	-
6	RD-
7	-
8	-



USB Mini-B Connection



SL1 Connection




SL1

Ν°	RS 232	RS 485
1	RxD	N.C.
2	TxD	N.C.
3	RTS	N.C.
4	N.C.	D1
5	N.C.	D0
6	стѕ	N.C.
7	N.C*.	5 Vdc
8	Common	Common

N.C.: not connected


^{*: 5} Vdc delivered by the controller. Do not connect.



Performance Curves

Derating Curves


Embedded Digital Inputs (No Cartridge)



X: Ambient temperature

Y: Input simultaneous ON ratio

Embedded Digital Inputs (with Cartridge)




X: Ambient temperature

Y: Input simultaneous ON ratio

Derating Curves


Embedded Digital Outputs (No Cartridge)



X: Ambient temperature

Y: Output simultaneous ON ratio

Embedded Digital Outputs (with Cartridge)



X: Ambient temperature

Y: Output simultaneous ON ratio