# **Product data sheet**

Specification





variable speed drive, Altivar Machine ATV340, 37kW, heavy duty, 400V, 3 phases, Ethernet

ATV340D37N4E

Product availability: Stock - Normally stocked in distribution

Price\*: 6,265.80 USD

#### Main

Range Of Product	Altivar Machine ATV340	
Product Or Component Type	Variable speed drive	
Product Specific Application	Machine	
Variant	Standard version	
Mounting Mode	Wall mount	
Communication Port Protocol	Modbus TCP Modbus serial EtherNet/IP	
Option Card	communication module, PROFINET communication module, DeviceNet communication module, CANopen communication module, EtherCAT	
Phase	3 phase	
Supply Frequency	5060 Hz +/- 5 %	
[Us] Rated Supply Voltage	380480 V - 1510 %	
Nominal Output Current	74.5 A	
Motor Power Kw	45 kW normal duty 37 kW heavy duty	
Maximum Horse Power Rating	60 hp normal duty 50 hp heavy duty	
Emc Filter	Class C3 EMC filter integrated	
Ip Degree Of Protection	IP20	
Degree Of Protection	UL type 1	

## Complementary

Discrete Input Number	8	
Discrete Input Type	PTI safe torque off 030 kHz, 24 V DC 30 V) DI1DI5 programmable as pulse input, 24 V DC 30 V)3.5 kOhm programmable	
Number Of Preset Speeds	16 preset speeds	
Discrete Output Number	1.0	
Discrete Output Type	Programmable output DQ1, DQ2 30 V DC 100 mA	
Analogue Input Number	3	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Analogue Input Type	Al1 software-configurable current 020 mA 250 Ohm 12 bits Al1 software-configurable temperature probe or water level sensor Al1 software-configurable voltage 010 V DC 31.5 kOhm 12 bits Al2 software-configurable voltage - 1010 V DC 31.5 kOhm 12 bits	
Analogue Output Number	2	
Analogue Output Type	Software-configurable voltage AQ1, AQ2 010 V DC 470 Ohm 10 bits Software-configurable current AQ1, AQ2 020 mA 500 Ohm 10 bits	
Relay Output Number	3	
Output Voltage	<= power supply voltage	
Relay Output Type	Relay outputs R1A Relay outputs R1C 100000 cycles Relay outputs R2A Relay outputs R2C 100000 cycles	
Maximum Switching Current	Relay output R1C resistive, cos phi = 1 3 A 250 V AC Relay output R1C resistive, cos phi = 1 3 A 30 V DC Relay output R1C inductive, cos phi = 0.4 7 ms 2 A 250 V AC Relay output R1C inductive, cos phi = 0.4 7 ms 2 A 30 V DC Relay output R2C resistive, cos phi = 1 5 A 250 V AC Relay output R2C resistive, cos phi = 1 5 A 30 V DC Relay output R2C resistive, cos phi = 1 5 A 30 V DC Relay output R2C inductive, cos phi = 0.4 7 ms 2 A 250 V AC Relay output R2C inductive, cos phi = 0.4 7 ms 2 A 30 V DC	
Minimum Switching Current	Relay output R1B 5 mA 24 V DC Relay output R2C 5 mA 24 V DC	
Physical Interface	2-wire RS 485	
Connector Type	3 RJ45	
Method Of Access	Slave Modbus RTU Slave Modbus TCP	
Transmission Rate	4.8 kbit/s 9.6 kbit/s 19.2 kbit/s 38.4 kbit/s	
Transmission Frame	RTU	
Number Of Addresses	1247	
Data Format	8 bits, configurable odd, even or no parity	
Type Of Polarization	No impedance	
4 Quadrant Operation Possible	True	
Asynchronous Motor Control Profile	Optimized torque mode Variable torque standard Constant torque standard	
Synchronous Motor Control Profile	Reluctance motor Permanent magnet motor	
Pollution Degree	2 IEC 61800-5-1	
Maximum Output Frequency	0.599 kHz	
Acceleration And Deceleration Ramps	Linear adjustable separately from 0.019999 s S, U or customized	
Motor Slip Compensation	Adjustable Can be suppressed Automatic whatever the load Not available in permanent magnet motor law	
Switching Frequency	216 kHz adjustable 416 kHz with derating factor	
Nominal Switching Frequency	4 kHz	
Braking To Standstill	By DC injection	
Brake Chopper Integrated	True	

Line Current	79.8 A 380 V normal duty)
	69.1 A 480 V normal duty) 67.1 A 380 V heavy duty)
	59.0 A 480 V heavy duty)
	33.0 A 400 V ficavy duty)
Line Current	79.8 A 380 V with internal line choke normal duty)
	69.1 A 480 V with internal line choke normal duty)
	67.1 A 380 V with internal line choke heavy duty)
	59 A 480 V with internal line choke heavy duty)
	67.1 A
	59.0 A
Maximum Input Current Per Phase	79.8 A
Maximum Output Voltage	480 V
Apparent Power	57.4 kVA 480 V normal duty)
	49.1 kVA 480 V heavy duty)
Maximum Transient Current	105 6 A 60 a parmal duty)
Maximum Transient Gurrent	105.6 A 3 a normal duty)
	105.6 A 2 s normal duty) 111.8 A 60 s heavy duty)
	· · · · · · · · · · · · · · · · · · ·
	111.8 A 2 s heavy duty)
Electrical Connection	Screw terminal 0.751.5 mm² control
	Screw terminal 3550 mm² line side
	Screw terminal 3550 mm² DC bus
	Screw terminal 50 mm² motor
Prospective Line Isc	50 kA
Base Load Current At High Overload	74.5 A
Base Load Current At Low Overload	88.0 A
Power Dissipation In W	Natural convection 90 W 380 V 4 kHz heavy duty)
	Forced convection 796 W 380 V 4 kHz heavy duty)
	Natural convection 105 W 380 V 4 kHz normal duty)
	Forced convection 943 W 380 V 4 kHz normal duty)
Electrical Connection	Control screw terminal 0.751.5 mm² AWG 18AWG 16
	Line side screw terminal 3550 mm² AWG 2AWG 1
	DC bus screw terminal 3550 mm² AWG 3AWG 1
	Motor screw terminal 50 mm² AWG 1
With Safety Function Safely	True
Limited Speed (SIs) With Safety Function Safe Brake	True
Management (Sbc/Sbt)	Title
With Safety Function Safe Operating Stop (Sos)	False
With Safety Function Safe Position (Sp)	False
With Safety Function Safe Programmable Logic	False
With Safety Function Safe Speed Monitor (Ssm)	False
With Safety Function Safe Stop 1 (Ss1)	True
With Sft Fct Safe Stop 2 (Ss2)	False
With Safety Function Safe Torque Off (Sto)	True
With Safety Function Safely Limited Position (SIp)	False
With Safety Function Safe Direction (Sdi)	False

Protection Type	Thermal protection motor		
	Safe torque off motor		
	Motor phase loss motor		
	Thermal protection drive		
	Safe torque off drive		
	Overheating drive		
	Overcurrent drive		
	Output overcurrent between motor phase and earth drive		
	Output overcurrent between motor phases drive		
	Short-circuit between motor phase and earth drive		
	Short-circuit between motor phases drive		
	Motor phase loss drive		
	DC Bus overvoltage drive		
	Line supply overvoltage drive		
	Line supply undervoltage drive		
	Input supply loss drive		
	Exceeding limit speed drive		
	Break on the control circuit drive		
Width	8.39 in (213.0 mm)		
Height	25.98 in (660.0 mm)		
Depth	10.31 in (262.0 mm)		
Net Weight	62.61 lb(US) (28.4 kg)		
Continuous Output Current	88 A 4 kHz normal duty		
	74.5 A 4 kHz heavy duty		

# **Environment**

Operating Altitude	<= 4800 m with current derating above 1000m	
Operating Position	Vertical +/- 10 degree	
Product Certifications	UL CSA TÜV EAC CTick	
Marking	CE	
Standards	IEC 61800-3 IEC 61800-5-1 IEC 60721-3 IEC 61508 IEC 13849-1 UL 618000-5-1 UL 508C IEC 61000-3-12	
Maximum Thdi	<48 % full load IEC 61000-3-12 <48 % 80 % load IEC 61000-3-12	
Assembly Style	With heat sink	
Electromagnetic Compatibility	Electrostatic discharge immunity test level 3 IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test level 3 IEC 61000-4-3 Electrical fast transient/burst immunity test level 4 IEC 61000-4-4 1.2/50 µs - 8/20 µs surge immunity test level 3 IEC 61000-4-5 Conducted radio-frequency immunity test level 3 IEC 61000-4-6	
Environmental Class (During Operation)	Class 3C3 according to IEC 60721-3-3 Class 3S3 according to IEC 60721-3-3	
Maximum Acceleration Under Shock Impact (During Operation)	150 m/s² at 11 ms	
Maximum Acceleration Under Vibrational Stress (During Operation)	10 m/s² at 13200 Hz	
Maximum Deflection Under Vibratory Load (During Operation)	1.5 mm at 213 Hz	
Permitted Relative Humidity (During Operation)	Class 3K5 according to EN 60721-3	
Volume Of Cooling Air	63402.43 Gal/hr(US) (240.0 m3/h)	

Type Of Cooling	Forced convection
Overvoltage Category	Class III
Regulation Loop	Adjustable PID regulator
Noise Level	63.5 dB
Pollution Degree	2
Ambient Air Transport Temperature	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	5122 °F (-1550 °C) without derating vertical position) 122140 °F (5060 °C) with derating factor vertical position)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Isolation	Between power and control terminals

# Ordering and shipping details

Category	US1CP4B22183
Discount Schedule	CP4B
Gtin	3606480967108
Returnability	Yes
Country Of Origin	US

# **Packing Units**

_	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.26 in (54 cm)
Package 1 Width	13.39 in (34 cm)
Package 1 Length	33.07 in (84 cm)
Package 1 Weight	82 89 lb(US) (37 6 kg)

# Sustainability Screen Premium

Green Premium<sup>TM</sup> label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Resource performance



Upgraded Components Available

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes


#### **Certifications & Standards**

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)  China Rohs Regulation China RoHS declaration  Environmental Disclosure Product Environmental Profile  Weee The product must be disposed on European Union markets following collection and never end up in rubbish bins.  Circularity Profile End of Life Information  WARNING: This product can expose you to chemicals including: Legal Scope)	REACh Declaration	
Environmental Disclosure  Product Environmental Profile  The product must be disposed on European Union markets following collection and never end up in rubbish bins.  Circularity Profile  End of Life Information	Pro-active compliance (Product out of EU RoHS legal scope)	
Weee The product must be disposed on European Union markets following collection and never end up in rubbish bins.  Circularity Profile End of Life Information	China RoHS declaration	
collection and never end up in rubbish bins.  Circularity Profile End of Life Information	Product Environmental Profile	
End of End midmator	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	
California Proposition 65 WARNING: This product can expose you to chemicals including: Le		
compounds, which is known to the State of California to cause can defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov		

#### **Dimensions Drawings**


#### **Dimensions**


#### Views: Front - Left - Rear



Mounting and Clearance

## Clearance





#### Dimensions in mm


X1	X2	X3
≥ 100	≥ 100	≥ 10

#### Dimensions in in.

X1	X2	X3
≥ 3.94	≥ 3.94	<sup>▶</sup> 0.39


#### **Mounting Types**

#### Mounting Type A: Side by Side IP20



Possible, up to 50 °C, 2 drives only

#### Mounting Type B: Individual IP20




a 110 mm (4.33 in.)

#### Connections and Schema

#### **Connections and Schema**

# Three-Phase Power Supply with Upstream Breaking via Line Contactor Without Safety Function STO

Connection diagrams conforming to standards ISO13849 category 1 and IEC/EN 61508 capacitySIL1, stopping category 0 in accordance with standard IEC/EN 60204-1.



(1) Use relay output R1 set to operating state Fault to switch Off the product once an error is detected.


A1: Drive

KM1: Line ContactorQ2, Q3: Circuit breakers

S1: PushbuttonS2: Emergency stop

T1: Transformer for control part

#### Three-Phase Power Supply with Downstream Breaking via Switch Disconnector



## **Product data sheet**


# ATV340D37N4E

(1) Use relay output R1 set to operating state Fault to switch Off the product once an error is detected.

A1: Drive


Q1: Switch disconnector

#### **Sensor Connection**



It is possible to connect either 1 or 3 sensors on terminals Al1/Al3.

#### **Control Block Wiring Diagram**




- (1) Safe Torque Off
- (2) Analog Output
- (3) Digital Input
- (4) Reference potentiometer
- (5) Analog Input
- (6) Digital Output
- (7) 0-10 Vdc, x-20 mA
- (8) 0-10 Vdc, -10 Vdc...+10 Vdc

A1: ATV340 Drive


R1A, R1B, R1C: Fault relay
R2A, R2C: Sequence relay
R3A, R3C: Sequence relay

#### **Digital Inputs Wiring**


Switch Set to SRC (Source) Position Using the Output Power Supply for the Digital Inputs




Switch Set to SRC (Source) Position and Use of an External Power Supply for the DIs



Switch Set to SK (Sink) Position Using the Output Power Supply for the Digital Inputs



Switch Set to EXT Position Using an External Power Supply for the DIs




13

#### **Digital Outputs Wiring**

#### **Digital Outputs: Internal Supply**

Positive Logic, Source, European Style, DQ switches to +24V



(1) Relay or valve


#### Negative Logic, Sink, Asian Style, DQ switches to 0V



(1) Relay or valve


#### **Digital Outputs: External Supply**

Positive Logic, Source, European Style, DQ switches to +24V



(1) Relay or valve

#### Negative Logic, Sink, Asian Style, DQ switches to 0V




(1) Relay or valve

## **Product data sheet**

#### ATV340D37N4E


#### Performance Curves

#### **Open Loop Applications**



- 1: Self-cooled motor: continuous useful torque
- 2: Force-cooled motor: continuous useful torque
- 3: Overtorque for 60 s maximum
- 4: Torque in overspeed at constant power

#### **Closed Loop Applications**



- 1: Self-cooled motor: continuous useful torque
- 2: Force-cooled motor: continuous useful torque
- 3: Overtorque for 60 s maximum
- 4: Torque in overspeed at constant power