

off-delay timing relay with control contact - 0.05..1 s - 24 V AC DC - 1OC

RE7RM11BU

! Discontinued on: Jan 23, 2021

① Discontinued

Main

| Range Of Product | Zelio Time |
|---------------------------|-------------------------|
| Product Or Component Type | Industrial timing relay |
| Component Name | RE7 |
| Time Delay Type | С |
| Time Delay Range | 0.05 s300 h |

Complementary

| Discrete Output Type | Relay |
|--|---|
| Contacts Material | 90/10 silver nickel contacts |
| Width Pitch Dimension | 0.89 in (22.5 mm) |
| [Us] Rated Supply Voltage | 110240 V AC 50/60 Hz 24 V AC/DC 50/60 Hz 4248 V AC/DC 50/60 Hz |
| Voltage Range | 0.851.1 Us |
| Connections - Terminals | Screw terminals, 2 x 1.5 mm² flexible with cable end Screw terminals, 2 x 2.5 mm² flexible without cable end |
| Tightening Torque | 5.319.74 lbf.in (0.61.1 N.m) |
| Setting Accuracy Of Time Delay | +/- 10 % of full scale |
| Repeat Accuracy | +/- 0.2 % |
| Temperature Drift | < 0.07 %/°C |
| Voltage Drift | < 0.2 %/V |
| Minimum Pulse Duration | 20 ms |
| Reset Time | 50 ms |
| Maximum Switching Voltage | 250 V AC/DC |
| Mechanical Durability | 20000000 cycles |
| [Ith] Conventional Free Air Thermal Current | 8 A |
| Maximum [le] Rated Operational Current | 2 A DC-13 24 V 158 °F (70 °C) IEC 60947-5-1/1991/VDE 0660 0.1 A DC-13 250 V 158 °F (70 °C) IEC 60947-5-1/1991/VDE 0660 0.2 A DC-13 115 V 158 °F (70 °C) IEC 60947-5-1/1991/VDE 0660 3 A AC-15 158 °F (70 °C) IEC 60947-5-1/1991/VDE 0660 |
| Minimum Switching Capacity | 10 mA 12 V |
| Input Voltage | < 60 V X1Z2 < 60 V Y1Z2 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Maximum Switching Current | 1 mA X1Z2) 1 mA Y1Z2) |
|--------------------------------|---|
| | |
| Input Compatibility | 3/4 wires sensors PNP/NPN without internal load <164.04 ft (50 m) X1Z2 3/4 wires sensors PNP/NPN without internal load <164.04 ft (50 m) Y1Z2 |
| Potentiometer Characteristic | Linear 47 kOhm +/- 20 %), 0.2 W 82.02 ft (25 m) Z1Z2 |
| Marking | CE |
| Overvoltage Category | III IEC 60664-1 |
| [Ui] Rated Insulation Voltage | 250 V between contact circuit and control inputs IEC 250 V between contact circuit and power supply IEC 300 V between contact circuit and control inputs CSA 300 V between contact circuit and power supply CSA |
| Supply Disconnection Value | > 0.1 Uc |
| Operating Position | Any position without derating |
| Surge Withstand | 2 kV IEC 61000-4-5 level 3 |
| Power Consumption In Va | 0.7 VA 24 V 1.6 VA 48 V 1.8 VA 110 V 8.5 VA 240 V |
| Maximum Power Consumption In W | 0.5 W 24 V 1.2 W 48 V |
| Terminal Description | (15-16-18)OC_OFF ALT (B1-A2)CO (Z1)UNUSED (Z2)UNUSED (X1)UNUSED (Y1)UNUSED |
| Height | 3.07 in (78 mm) |
| Width | 0.89 in (22.5 mm) |
| Depth | 3.15 in (80 mm) |
| Net Weight | 0.33 lb(US) (0.15 kg) |

Environment

| Limitollilett | |
|---------------------------------------|--|
| Immunity To Microbreaks | 3 ms |
| Standards | EN/IEC 61812-1 |
| Product Certifications | UL GL CSA |
| Ambient Air Temperature For Storage | -40185 °F (-4085 °C) |
| Ambient Air Temperature For Operation | -4140 °F (-2060 °C) |
| Relative Humidity | 1585 % 3K3 IEC 60721-3-3 |
| Vibration Resistance | 0.35 mm 1055 Hz)IEC 60068-2-6 |
| Shock Resistance | 15 gn 11 ms IEC 60068-2-27 |
| Ip Degree Of Protection | IP20 terminals) IP50 housing) |
| Pollution Degree | 3 IEC 60664-1 |
| Dielectric Strength | 2.5 kV |
| Non-Dissipating Shock Wave | 4.8 kV |
| Resistance To Electrostatic Discharge | 6 kV in contact IEC 61000-4-2 level 3 8 kV in air IEC 61000-4-2 level 3 |

| Resistance To Electromagnetic Fields | 9.14 V/m (10 V/m) IEC 61000-4-3 level 3 |
|--------------------------------------|--|
| Resistance To Fast Transients | 2 kV IEC 61000-4-4 level 3 |
| Disturbance Radiated/Conducted | CISPR 11 group 1 - class A CISPR 22 - class A |

Ordering and shipping details

| Category | 22376-RELAYS-MEASUREMENT(RM4) |
|-------------------|-------------------------------|
| Discount Schedule | CP2 |
| Gtin | 00785901481478 |
| Returnability | No |
| Country Of Origin | ID |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-----|
| Number Of Units In Package 1 | 1 |


Contractual warranty

Warranty 18 months


Dimensions Drawings

Width 22.5 mm

Rail Mounting



Screw Fixing



Product data sheet

RE7RM11BU


Connections and Schema

Internal Wiring Diagram

| A1 | 15 | B1 |
|-------|----------|-------|
| Z1 | | B2 |
| A2 B2 |] [A] | 18 15 |
| X1 | Ý1 | Z2 |
| 18 | 16 | A2 |

Recommended Application Wiring Diagram


Start by External Control



- 1 Supply
- **2** 12...48 V
- **3** 24 V

Recommended Application Wiring Diagram


Start by External Control




- 1 Supply
- **2** 12...48 V
- **3** 24 V

Control of Several Relays

Control of several relays with a single external control contact




Connection of an External Control Contact Without Using Terminal Z2



Direct current supply only.


It is advisable to follow the recommended wiring schemes detailed above if the restrictions given are taken into account.



Direct current supply only.


It is advisable to follow the recommended wiring schemes detailed above if the restrictions given are taken into account.

Connection 3-Wire NPN or PNP Sensor




Connection 3-Wire NPN or PNP Sensor Without Using Terminal Z2

Connection NPN




It is advisable to follow the recommended wiring schemes detailed above if the restrictions given are taken into account.

Connection PNP



It is advisable to follow the recommended wiring schemes detailed above if the restrictions given are taken into account.

Connection of Potentiometer




Connection Precautions



UNEXPECTED EQUIPMENT OPERATION

No galvanic isolation between supply terminals and control inputs.

Failure to follow these instructions can result in death, serious injury, or equipment damage.




13

Performance Curves

Performance Curves

A.C. Load Curve 1


Electrical durability of contacts on resistive loading millions of operating cycles



X Current broken in A Y Millions of operating cycles

A.C. Load Curve 2

Reduction factor k for inductive loads (applies to values taken from durability curve 1).



\boldsymbol{X} Power factor on breaking (cos $\boldsymbol{\varphi}$)

Y Reduction factor k

Example: An LC1-F185 contactor supplied with 115 V/50 Hz for a consumption of 55 VA or a current consumption equal to 0.1 A and $\cos \phi = 0.3$. For 0.1 A, curve 1 indicates a durability of approximately 1.5 million operating cycles. As the load is inductive, it is necessary to apply a reduction coefficient k to this number of cycles as indicated by curve 2.


For $\cos \phi = 0.3$: k = 0.6 The electrical durability therefore becomes:1.5 10^6 operating cycles x 0.6 = 900 000 operating cycles.



D. C. Load Limit Curve

Product data sheet

RE7RM11BU



- X Current in A
- Y Voltage in V
- **1** L/R = 20 ms
- 2 L/R with load protection diode
- 3 Resistive load


Technical Description

Function C: Off-Delay Relay with Control Signal


Description

After power-up and closing of the control contact C, the output R closes. When control contact C re-opens, timing T starts. At the end of the timing period, the output(s) R revert(s) to its/their initial state. The second output can be either timed or instantaneous

Function: 1 Output



Function: 2 Outputs



2 timed outputs (R1/R2) or 1 timed output (R1) and 1 instantaneous output (R2 inst.)

Legend

| | Relay de-energised |
|----------|--|
| | Relay energised |
| | Output open |
| | Output closed |
| С | Control contact |
| G | Gate |
| R | Relay or solid state output |
| R1/R2 | 2 timed outputs |
| R2 inst. | The second output is instantaneous if the right position is selected |
| Т | Timing period |
| Та - | Adjustable On-delay |
| Tr - | Adjustable Off-delay |
| U | Supply |