Product datasheet

Specification





logic controller, Modicon M221, 16 IO, 9 DI, 7 DO, relay, Ethernet

TM221CE16R

Main

Range Of Product	Modicon M221
Product Or Component Type	Logic controller
[Us] Rated Supply Voltage	100240 V AC
Discrete Input Number	9, discrete input conforming to IEC 61131-2 Type 1
Analogue Input Number	2 at 010 V
Discrete Output Type	Relay normally open
Discrete Output Number	7 relay
Discrete Output Voltage	5125 V DC 5250 V AC
Discrete Output Current	2 A

Complementary

oompromentary	
Discrete I/O Number	16
Maximum Number Of I/O Expansion Module	4 (local I/O-Architecture) 11 (remote I/O-Architecture)
Supply Voltage Limits	85264 V
Network Frequency	50/60 Hz
Inrush Current	40 A
Maximum Power Consumption In Va	49 VA at 100240 V with max number of I/O expansion module 33 VA at 100240 V without I/O expansion module
Power Supply Output Current	0.325 A 5 V for expansion bus 0.12 A 24 V for expansion bus
Discrete Input Logic	Sink or source (positive/negative)
Discrete Input Voltage	24 V
Discrete Input Voltage Type	DC
Analogue Input Resolution	10 bits
Lsb Value	10 mV
Conversion Time	1 ms per channel + 1 controller cycle time for analogue input analog input
Permitted Overload On Inputs	+/- 30 V DC for 5 min (maximum) for analog input +/- 13 V DC (permanent) for analog input
Voltage State 1 Guaranteed	>= 15 V for input
Voltage State 0 Guaranteed	<= 5 V for input
Discrete Input Current	7 mA for discrete input 5 mA for fast input

Input Impedance	3.4 kOhm for discrete input
	100 kOhm for analog input
	4.9 kOhm for fast input
Response Time	35 μs turn-off, I2I5 terminal(s) for input
•	10 ms turn-on for output
	10 ms turn-off for output
	5 µs turn-on, I0, I1, I6, I7 terminal(s) for fast input
	35 μs turn-on, other terminals terminal(s) for input
	5 μs turn-off, I0, I1, I6, I7 terminal(s) for fast input
	100 μs turn-off, other terminals terminal(s) for input
Configurable Filtering Time	0 ms for input
	3 ms for input
	12 ms for input
Output Valtage Limits	4051/100
Output Voltage Limits	125 V DC 277 V AC
	211 4 110
Maximum Current Per Output	6 A at COM 1
Common	7 A at COM 0
Absolute Accuracy Error	1/ 1 9/ of full cools for analog input
Absolute Accuracy Error	+/- 1 % of full scale for analog input
Electrical Durability	100000 cycles AC-12, 120 V, 240 VA, resistive
	100000 cycles AC-12, 240 V, 480 VA, resistive
	300000 cycles AC-12, 120 V, 80 VA, resistive
	300000 cycles AC-12, 240 V, 160 VA, resistive
	100000 cycles AC-15, cos phi = 0.35, 120 V, 60 VA, inductive
	100000 cycles AC-15, cos phi = 0.35, 240 V, 120 VA, inductive
	300000 cycles AC-15, cos phi = 0.35, 120 V, 18 VA, inductive
	300000 cycles AC-15, cos phi = 0.35, 240 V, 36 VA, inductive
	100000 cycles AC-14, cos phi = 0.7, 120 V, 120 VA, inductive
	100000 cycles AC-14, cos phi = 0.7, 240 V, 240 VA, inductive
	300000 cycles AC-14, cos phi = 0.7, 120 V, 36 VA, inductive
	300000 cycles AC-14, cos phi = 0.7, 240 V, 72 VA, inductive
	100000 cycles DC-12, 24 V, 48 W, resistive
	300000 cycles DC-12, 24 V, 16 W, resistive
	100000 cycles DC-13, 24 V, 24 W, inductive (L/R = 7 ms)
	300000 cycles DC-13, 24 V, 7.2 W, inductive (L/R = 7 ms)
Switching Frequency	20 switching operations/minute with maximum load
Mechanical Durability	20000000 cycles for relay output
Minimum Load	1 mA at 5 V DC for relay output
Protection Type	Without protection at 5 A
Reset Time	1 s
Memory Capacity	OFC LD for year analysis and data DAM with 40000 instructions
метогу Сарасіту	256 kB for user application and data RAM with 10000 instructions 256 kB for internal variables RAM
	200 KB TOT ITICITIAL VALIABLES TO TWI
Data Backed Up	256 kB built-in flash memory for backup of application and data
Data Storage Equipment	2 GB SD card (optional)
Battery Type	BR2032 or CR2032X lithium non-rechargeable
Backup Time	1 year at 25 °C (by interruption of power supply)
Execution Time For 1 Kinstruction	0.3 ms for event and periodic task
Execution Time Per Instruction	0.2 μs Boolean
Exct Time For Event Task	60 μs response time
Exct Time For Event Task Maximum Size Of Object Areas	255 %C counters 512 %KW constant words
	255 %C counters
	255 %C counters 512 %KW constant words
	255 %C counters 512 %KW constant words 255 %TM timers
Maximum Size Of Object Areas	255 %C counters 512 %KW constant words 255 %TM timers 512 %M memory bits 8000 %MW memory words
Maximum Size Of Object Areas Realtime Clock	255 %C counters 512 %KW constant words 255 %TM timers 512 %M memory bits 8000 %MW memory words With
Maximum Size Of Object Areas	255 %C counters 512 %KW constant words 255 %TM timers 512 %M memory bits 8000 %MW memory words

Counting Input Number	4 fast input (HSC mode) at 100 kHz 32 bits
Counter Function	Pulse/direction A/B Single phase
Integrated Connection Type	USB port with mini B USB 2.0 connector Non isolated serial link serial 1 with RJ45 connector and RS232/RS485 interface Ethernet with RJ45 connector
Supply	(serial)serial link supply: 5 V, <200 mA
Transmission Rate	1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 15 m for RS485 1.2115.2 kbit/s (115.2 kbit/s by default) for bus length of 3 m for RS232 480 Mbit/s for USB
Communication Port Protocol	USB port: USB - SoMachine-Network Non isolated serial link: Modbus master/slave - RTU/ASCII or SoMachine-Network Ethernet
Port Ethernet	10BASE-T/100BASE-TX 1 port with 100 m copper cable
Communication Service	DHCP client Ethernet/IP adapter Modbus TCP server Modbus TCP slave device Modbus TCP client
Local Signalling	1 LED (green) for PWR 1 LED (green) for RUN 1 LED (red) for module error (ERR) 1 LED (green) for SD card access (SD) 1 LED (red) for BAT 1 LED per channel (green) for I/O state 1 LED (green) for SL Ethernet network activity (green) for ACT Ethernet network link (yellow) for Link (Link Status)
Electrical Connection	removable screw terminal block for inputs removable screw terminal block for outputs terminal block, 3 terminal(s) for connecting the 24 V DC power supply connector, 4 terminal(s) for analogue inputs Mini B USB 2.0 connector for a programming terminal
Maximum Cable Distance Between Devices	Shielded cable: <10 m for fast input Unshielded cable: <30 m for output Unshielded cable: <30 m for digital input Unshielded cable: <1 m for analog input
Insulation	Between input and internal logic at 500 V AC Non-insulated between analogue input and internal logic Non-insulated between analogue inputs Between supply and ground at 1500 V AC Between sensor power supply and ground at 500 V AC Between input and ground at 500 V AC Between output and ground at 1500 V AC Between supply and internal logic at 2300 V AC Between sensor power supply and internal logic at 500 V AC Between between output and internal logic at 2300 V AC Between Ethernet terminal and internal logic at 500 V AC Between supply and sensor power supply at 2300 V AC
Marking	CE
Sensor Power Supply	24 V DC at 250 mA supplied by the controller
Mounting Support	Top hat type TH35-15 rail conforming to IEC 60715 Top hat type TH35-7.5 rail conforming to IEC 60715 plate or panel with fixing kit
Height	90 mm
Depth	70 mm
Width	95 mm
Net Weight	0.346 kg

Environment

Standards	IEC 61131-2
	UL 508 CAN/CSA C22.2 No. 213
	IACS E10
	ANSI/ISA 12-12-01
Product Certifications	cULus
	LR
	RCM
	EAC
	ABS DNV-GL
	CE
	UKCA
	cULus HazLoc
Environmental Characteristic	Ordinary and hazardous location
Resistance To Electrostatic	8 kV in air conforming to IEC 61000-4-2
Discharge	4 kV on contact conforming to IEC 61000-4-2
Resistance To Electromagnetic	10 V/m 80 MHz1 GHz conforming to IEC 61000-4-3
Fields	3 V/m 1.4 GHz2 GHz conforming to IEC 61000-4-3
	1 V/m 22.7 GHz conforming to IEC 61000-4-3
Resistance To Magnetic Fields	30 A/m 50/60 Hz conforming to IEC 61000-4-8
Resistance To Fast Transients	2 kV (power lines) conforming to IEC 61000-4-4
	2 kV (relay output) conforming to IEC 61000-4-4
	1 kV (I/O) conforming to IEC 61000-4-4
	1 kV (Ethernet line) conforming to IEC 61000-4-4
	1 kV (serial link) conforming to IEC 61000-4-4
Surge Withstand	2 kV power lines (AC) common mode conforming to IEC 61000-4-5
	2 kV relay output common mode conforming to IEC 61000-4-5
	1 kV I/O common mode conforming to IEC 61000-4-5
	1 kV shielded cable common mode conforming to IEC 61000-4-5 0.5 kV power lines (DC) differential mode conforming to IEC 61000-4-5
	1 kV power lines (AC) differential mode conforming to IEC 61000-4-5
	1 kV relay output differential mode conforming to IEC 61000-4-5
	0.5 kV power lines (DC) common mode conforming to IEC 61000-4-5
Resistance To Conducted	10.1/.0.15 90.MHz conforming to IEC 61000.4.6
Disturbances	10 V 0.1580 MHz conforming to IEC 61000-4-6 3 V 0.180 MHz conforming to Marine specification (LR, ABS, DNV, GL)
	10 V spot frequency (2, 3, 4, 6.2, 8.2, 12.6, 16.5, 18.8, 22, 25 MHz) conforming to
	Marine specification (LR, ABS, DNV, GL)
Electromagnetic Emission	Conducted emissions - test level: 79 dBμV/m QP/66 dBμV/m AV (power lines (AC))
	at 0.150.5 MHz conforming to IEC 55011
	Conducted emissions - test level: 73 dBµV/m QP/60 dBµV/m AV (power lines (AC))
	at 0.5300 MHz conforming to IEC 55011
	Conducted emissions - test level: 12069 dBµV/m QP (power lines) at 10150 kHz conforming to IEC 55011
	Conducted emissions - test level: 63 dBµV/m QP (power lines) at 1.530 MHz
	conforming to IEC 55011
	Radiated emissions - test level: 40 dBμV/m QP class A (10 m) at 30230 MHz
	conforming to IEC 55011
	Conducted emissions - test level: 7963 dBµV/m QP (power lines) at 1501500 kHz conforming to IEC 55011
	Radiated emissions - test level: 47 dBµV/m QP class A (10 m) at 2001000 MHz
	conforming to IEC 55011
Immunity To Microbreaks	10 ms
Ambient Air Temperature For	-1055 °C (horizontal installation)
Operation	-1035 °C (vertical installation)
Ambient Air Temperature For Storage	-2570 °C
Relative Humidity	1095 %, without condensation (in operation)
	1095 %, without condensation (in operation)
Ip Degree Of Protection	IP20 with protective cover in place
Pollution Degree	<= 2
Operating Altitude	02000 m
Storage Altitude	03000 m

Vibration Resistance	3.5 mm at 58.4 Hz on symmetrical rail 3.5 mm at 58.4 Hz on panel mounting 1 gn at 8.4150 Hz on symmetrical rail 1 gn at 8.4150 Hz on panel mounting
Shock Resistance	98 m/s² for 11 ms

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.829 cm
Package 1 Width	14.04 cm
Package 1 Length	14.181 cm
Package 1 Weight	590.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	28.9 cm
Package 2 Width	39.5 cm
Package 2 Length	57.4 cm
Package 2 Weight	12.771 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	240
Package 3 Height	105.0 cm
Package 3 Width	120.0 cm
Package 3 Length	80.0 cm
Package 3 Weight	164 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards


Weee	The product must be disposed on European Union markets following specific was collection and never end up in rubbish bins	
Environmental Disclosure	Product Environmental Profile	
China Rohs Regulation	China RoHS declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
Reach Regulation	REACh Declaration	


Product datasheet

TM221CE16R

Dimensions Drawings

Dimensions






Product datasheet


TM221CE16R

Mounting and Clearance

Mounting on a Rail





Direct Mounting on a Panel Surface



(1) Install a mounting strip


Mounting Hole Layout






Mounting

Correct Mounting Position




Acceptable Mounting Position



Incorrect Mounting Position









Clearance








Connections and Schema


Digital Inputs

Wiring Diagram (Positive Logic)



(*) Type T fuse

Wiring Diagram (Negative Logic)



(*) Type T fuse


Connection of the Fast Inputs



10, 11, 16, 17


Relay Outputs

Negative Logic (Sink)




- (*) Type T fuse
- (1) The COM1 and COM2 terminals are not connected internally.
- (2) To improve the life time of the contacts, and to protect from potential inductive load damage, you must connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load
- B Sink wiring (negative logic)


Positive Logic (Source)



- (*) Type T fuse
- (1) The COM1 and COM2 terminals are not connected internally.
- (2) To improve the life time of the contacts, and to protect from potential inductive load damage, you must connect a free wheeling diode in parallel to each inductive DC load or an RC snubber in parallel of each inductive AC load
- A Source wiring (positive logic)

Analog Inputs






The (-) poles are connected internally.

Pin	Wire Color	
0 V	Black	
AN1	Red	
0 V	Black	
AN0	Red	


Ethernet Connection




Pin N°	Signal
1	TD+
2	TD-
3	RD+
4	-
5	-
6	RD-
7	-
8	-



USB Mini-B Connection



SL1 Connection




SL1

Ν°	RS 232	RS 485
1	RxD	N.C.
2	TxD	N.C.
3	RTS	N.C.
4	N.C.	D1
5	N.C.	D0
6	стѕ	N.C.
7	N.C*.	5 Vdc
8	Common	Common

N.C.: not connected


 $[\]ensuremath{^*}$: 5 Vdc delivered by the controller. Do not connect.



Performance Curves

Derating Curves


Embedded Digital Inputs (No Cartridge)



X: Ambient temperature

Y: Input simultaneous ON ratio

Embedded Digital Inputs (with Cartridge)



X: Ambient temperature

Y: Input simultaneous ON ratio