

# Product data sheet

Specifications



## Head for key selector switch, Harmony XB5, XB4, Ø22 mm 3 position stay put 421E

ZB5AG312

⚠ Discontinued on: Oct 20, 2020

⚠ Discontinued

### Main

|                               |                              |
|-------------------------------|------------------------------|
| Range Of Product              | Harmony XB5                  |
| Product Or Component Type     | Head for key selector switch |
| Device Short Name             | ZB5                          |
| Bezel Material                | Dark grey plastic            |
| Mounting Diameter             | 22 mm                        |
| Head Type                     | Standard                     |
| Sale Per Indivisible Quantity | 1                            |
| Shape Of Signaling Unit Head  | Round                        |
| Type Of Operator              | stay put                     |
| Operator Profile              | Black key switch             |
| Operator Position Information | 3 positions +/- 45°          |
| Type Of Keylock               | Key 421E                     |
| Key Withdrawal Position       | Center                       |

### Complementary

|                             |   |
|-----------------------------|---|
| Cad Overall Width           | 29 mm   |
| Cad Overall Height          | 29 mm   |
| Cad Overall Depth           | 72 mm   |
| Net Weight                  | 0.057 kg  |
| Mechanical Durability       | 1000000 cycles  |
| Station Name                | XALD 1...5 cut-outs<br>XALK 2...5 cut-outs  |
| Electrical Composition Code | C4 for <6 contacts using single and double blocks in front mounting<br>C5 for <5 contacts using single blocks in front mounting<br>C6 for <5 contacts using single and double blocks in front mounting<br>C7 for <4 contacts using single blocks in front mounting<br>C8 for <4 contacts using single and double blocks in front mounting<br>C11 for <3 contacts using single blocks in front mounting<br>C3 for <6 contacts using single blocks in front mounting<br>SF1 for <3 contacts using single blocks in front mounting<br>SR1 for <3 contacts using single blocks in rear mounting |
| Device Presentation         | Basic element   |

### Environment

|                      |    |
|----------------------|----|
| Protective Treatment | TH |
|----------------------|----|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                       |  |
|---------------------------------------|--|
| Ambient Air Temperature For Storage   | -40...70 °C  |
| Ambient Air Temperature For Operation | -40...70 °C  |
| Overvoltage Category                  | Class II conforming to IEC 60536   |
| Ip Degree Of Protection               | IP66 conforming to IEC 60529<br>IP67<br>IP69<br>IP69K  |
| Nema Degree Of Protection             | NEMA 13<br>NEMA 4X   |
| Resistance To High Pressure Washer    | 7000000 Pa at 55 °C, distance : 0.1 m  |
| Ik Degree Of Protection               | IK06 conforming to IEC 50102   |
| Standards                             | EN/IEC 60947-1<br>JIS C8201-5-1<br>CSA C22.2 No 14<br>EN/IEC 60947-5-1<br>UL 508<br>EN/IEC 60947-5-4<br>JIS C8201-1  |
| Product Certifications                | UL listed<br>CSA<br>BV<br>GL<br>DNV<br>LROS (Lloyds register of shipping)  |
| Vibration Resistance                  | 5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6   |
| Shock Resistance                      | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27<br>50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free


✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

|                           |   |
|---------------------------|---|
| Reach Regulation          | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a>  |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile       | <a href="#">End of Life Information</a>   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

Dimensions Drawings

Dimensions



Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended ( $\text{Ø}22.3 \begin{smallmatrix} +0.4 \\ 0 \end{smallmatrix}$ ) / Ø0.89 in. recommended ( $\text{Ø}0.88 \text{ in.} \begin{smallmatrix} +0.016 \\ 0 \end{smallmatrix}$ )

| Connections                                   | a in mm | a in in. | b in mm | b in in. |
|---|---------|----------|---------|----------|
| By screw clamp terminals or plug-in connector | 40      | 1.57     | 30      | 1.18     |
| By Faston connectors                          | 45      | 1.77     | 32      | 1.26     |
| On printed circuit board                      | 30      | 1.18     | 30      | 1.18     |

Detail of Lug Recess



- (1) Diameter on finished panel or support
- (2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.
- (3) Ø22.5 mm recommended ( $\text{Ø}22.3 \begin{smallmatrix} +0.4 \\ 0 \end{smallmatrix}$ ) / Ø0.89 in. recommended ( $\text{Ø}0.88 \text{ in.} \begin{smallmatrix} +0.016 \\ 0 \end{smallmatrix}$ )

Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection

Panel Cut-outs (Viewed from Installer’s Side)



A: 30 mm min. / 1.18 in. min.

B: 40 mm min. / 1.57 in. min.

Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)

Dimensions in mm



A: 30 mm min.  
B: 40 mm min.  
Dimensions in in.



A: 1.18 in. min.

B: 1.57 in. min.

### General Tolerances of the Panel and Printed Circuit Board


The cumulative tolerance must not exceed 0.3 mm / 0.012 in.:  $T1 + T2 = 0.3$  mm max.

### Installation Precautions

- Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm  $\pm 0.1$  / 0.88 in.  $\pm 0.004$
- Orientation of body/fixing collar ZB5AZ009:  $\pm 2^\circ 30'$  (excluding cut-outs marked **a** and **b**).
- Tightening torque of screws ZBZ006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB5AZ079 fixing collar/pillar and its fixing screws:
  - every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
  - with each selector switch head (ZB5AD•, ZB5AJ•, ZB5AG•).

The fixing centers marked **a** and **b** are diagonally opposed and must align with those marked **4** and **5**.





- (1) Head ZB5AD•
- (2) Panel
- (2) Nut
- (4) Printed circuit board

**Mounting of Adapter (Socket) ZBZ01•**

- 1 2 elongated holes for ZBZ006 screw access
- 2 1 hole  $\varnothing 2.4 \text{ mm} \pm 0.05 / 0.09 \text{ in.} \pm 0.002$  for centring adapter ZBZ01•
- 3  $8 \times \varnothing 1.2 \text{ mm} / 0.05 \text{ in.}$  holes
- 4 1 hole  $\varnothing 2.9 \text{ mm} \pm 0.05 / 0.11 \text{ in.} \pm 0.002$ , for aligning the printed circuit board (with cut-out marked a)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked b)
- 6 4 holes  $\varnothing 2.4 \text{ mm} / 0.09 \text{ in.}$  for clipping in adapter ZBZ01•

Dimensions An + 18.1 relate to the  $\varnothing 2.4 \text{ mm} \pm 0.05 / 0.09 \text{ in.} \pm 0.002$  holes for centring adapter ZBZ01•.

Technical Description

Electrical Composition Corresponding to Code C4

---



Electrical Composition Corresponding to Code C5

---




Electrical Composition Corresponding to Code C6

---



Electrical Composition Corresponding to Code C7

---




Electrical Composition Corresponding to Code C8

---



Electrical Composition Corresponding to Code C3

---



Electrical Composition Corresponding to Codes C9, C11, SF1 and SR1





Legend

---

Single contact



Double contact



Light block






Possible location



Sequence of Contacts Fitted to 3-position Selector Switch Body





Position 315°



|          |          |        |   |   |        |
|----------|----------|--------|---|---|--------|
| Push     | Position | Top    |  |   |        |
|          |          | Bottom |  |  |        |
|          | Location |        | Left  | Centre  | Right  |
|          | State    |        | 1   | 1   | 0      |
|          |          |        |   |   |        |
| Contacts | N/O      |        | closed  | closed  | open   |
|          | N/C      |        | open  | open  | closed |




Position 0°



|          |          |        |   |   |   |
|----------|----------|--------|---|---|---|
| Push     | Position | Top    |  |   |   |
|          |          | Bottom |  |  |  |
|          | Location |        | Left  | Centre  | Right   |
|          | State    |        | 0   | 0   | 0   |
|          |          |        |   |   |   |
| Contacts | N/O      |        | open  | open  | open  |
|          | N/C      |        | closed  | closed  | closed  |

Position 45°



|          |          |        |   |   |        |
|----------|----------|--------|---|---|--------|
| Push     | Position | Top    |  |   |        |
|          |          | Bottom |  |  |        |
|          | Location |        | Left  | Centre  | Right  |
|          | State    |        | 0   | 1   | 1      |
|          |          |        |   |   |        |
| Contacts | N/O      |        | open  | closed  | closed |
|          | N/C      |        | closed  | open  | open   |